



Product sheet  
AC-2000 3G

- Features**
- Large display
  - Convenient user control
  - High performance measurement and control processes
  - SD card enabling simplified software updates
  - Support for
    - CO2 control
    - Various ventilation modes
    - Multiple exhaust, tunnel, stir and other fans
    - Multiple heating methods
    - Various types of curtains/inlets/dampers
    - Extended lighting, feeding and watering functionalities
    - Extended cooling and fogging functionalities
  - Flexible sensor assignment
  - 20 relays (28 when used in conjunction with an REB-8)
  - Extended data collection capabilities
  - Future connectivity and support for feed bin weighing
  - Flexible sensor assignment

# AC-2000 3G

AC-2000 3G, the next generation AC-2000 controller, provides a cost-effect, computerized control solution for poultry and swine farmers. Housed in the same hardware as the legacy AC-2000, the AC-2000 3G features an advanced software package that enables a host of new features.

As an option, the AC-2000 3G Panel Mount edition can be installed directly into an electrical cabinet. This capability reduces costs for farmers wanting to install their controllers in this manner.



Panel Mount



AC-2000 3G

## INPUT

- Temperature Sensors
- Humidity Sensor
- Pressure sensor
- CO2 sensor
- Bird scale
- Feed count
- Water meter
- Auxiliary alarm
- Potentiometers feedback

## LOCAL NETWORKS

- Wired
- Wireless

## REMOTE COMMUNICATION

- PC management
- Line modem
- Cellular & text messages
- Internet connection
- Browser management

## OUTPUT

- Light dimmer
- All sorts of fans
- All sorts of heaters
- Alarm
- Cooling systems
- Foggers
- Feeder
- Curtains
- Inlet - side, wall & attic
- Water



**Australia** Phone +61 2 8843 1594, [agh.info@munters.com.au](mailto:agh.info@munters.com.au), **Brazil** Phone +55 41 3317 5050, [contato@munters.com](mailto:contato@munters.com), **Canada** Phone +1 517 676 7070, [aghort.info@munters.com](mailto:aghort.info@munters.com), **China** Phone +86 10 8048 3493, [marketing@munters.cn](mailto:marketing@munters.cn), **Denmark** Phone +45 98 623 311, [aghort@munters.dk](mailto:aghort@munters.dk), **Germany** +49 (0) 25 58 - 93 92-0, **India** Phone +91 20 6681 8900, [info@munters.in](mailto:info@munters.in), **Indonesia** Phone +66 2 642 2670, [info@munters.co.th](mailto:info@munters.co.th), **Israel** Phone +972 3 920 6200, [info@munters.co.il](mailto:info@munters.co.il), **Italy** Phone +39 0183 5211, [info@munters.it](mailto:info@munters.it), **Japan** Phone +81 3 5970 0021, [mkk@munters.jp](mailto:mkk@munters.jp), **Korea** Phone +82 2 7618 701, [munters@munters.co.kr](mailto:munters@munters.co.kr), **Mexico** Phone +52 818 2625 400, [dhinfo@munters.com](mailto:dhinfo@munters.com), **Singapore** Phone +65 7 446 828, [info@munters.com.sg](mailto:info@munters.com.sg), **South Africa and Sub-Sahara Countries** Phone +27 11 997 2000, [info@munters.co.za](mailto:info@munters.co.za), **Spain** Phone +39 0183 5211, [info@munters.it](mailto:info@munters.it), **Sweden** Phone +46 8 6266 300, [info@munters.se](mailto:info@munters.se), **Thailand** Phone +66 2 6422 670, [info@munters.co.th](mailto:info@munters.co.th), **Turkey** Phone +90 262 7513 750, [info@muntersform.com](mailto:info@muntersform.com), **USA** Phone +1 517 676 7070, [aghort.info@munters.com](mailto:aghort.info@munters.com), **Export & Other countries** Phone +39 0183 5211, [info@munters.it](mailto:info@munters.it)

Your closest distributor