


400V 3 50Hz




400V 50Hz

400V 9kW

T - Thermostat
 B - Switch
 M - Motor
 TV - Safety thermostat
 D - Heating element (230V 3000W)
 T1 - Time-delay thermostat

SWITCH

- ⊖ OFF
- ⊗ POS.5
- ⊕ POS.5+2
- ⊕⊕ POS.5+2+3



0																			0°
1	⊗																		90°
2	⊗	⊗																	180°
3	⊗	⊗	⊗																270°

00	04/12/09	First issue						D. Fulcheri
Rev.No	Date	Description					Drawer	
Linear dimension range	up to 6	over 6 up to 30	over 30 up to 120	over 120 up to 400	over 400 up to 1000	over 1000 up to 2000	over 2000 up to 4000	
tolerance limits	±0.3	±0.5	±0.6	±1.2	±2	±3	±4	

Description		Schema elettrico RPL 9 FT (made in China)		Drawing No		SCH090	
		RPL 9 FT wiring diagram (made in China)		File name		SCH09000	
Material		-		Drawer		D. Fulcheri	
Thickness		-mm		Weight		Latest revision approved by	
				-kg		P. A. Oda	
Drawing scale		-		Date		04/12/2009	
				DIMENSIONS WITHOUT TOLERANCE LIMITS:		-	
				ROUGH PRECISION LEVEL		-	
				UNI EN 22769-1/2		-	

Munters
 MUNTERS ITALY S.p.A. - Mondovì
 This drawing is exclusive property of MUNTERS ITALY S.p.A.. Any vision, reproduction or release without written authorization by MUNTERS ITALY S.p.A. is ABSOLUTELY FORBIDDEN