



Munters Data Centre Projects Global

Project Location	Installed	Customer	Product Description	Equipment Location	IT Cooling load	Qty
AMER						
Pennsylvania	2017	Enterprise	Oasis IEC	Rooftop	365	1
Nevada	2017	Colocation	Oasis IEC	Outside Perimeter on Steel Dunnage	1200	4
Michigan	2017	Colocation	Oasis IEC	Outside Perimeter on Steel Dunnage	316	1
North Carolina	2017	Enterprise	Oasis IEC	Outside Perimeter on Concrete pad	15480	36
Washington	2017	Enterprise	Oasis IEC	Rooftop	494	2
Minnesota	2017	Colocation	Oasis IEC	Rooftop	873	3
Colorado	2017	Enterprise	Oasis IEC	Rooftop	3450	36
Washington	2016	Colocation	Oasis IEC	Rooftop	14027	36
Washington	2016	Colocation	Oasis IEC	Rooftop	1914	7
Utah	2016	Enterprise	Oasis IEC	Rooftop	2,328	8
Minnesota	2016	Colocation	Oasis IEC	Rooftop	1455	5
North Carolina	2016	Enterprise	Oasis IEC	Outside Perimeter on Concrete pad	7740	18
West Virginia	2016	Enterprise	Oasis IEC	Outside Perimeter on Concrete pad	478	2
California	2016	Enterprise	Oasis IEC	Rooftop	1080	4
Michigan	2016	Colocation	Oasis IEC	Outside Perimeter on Steel Dunnage	948	3
Pennsylvania	2015	Enterprise	Oasis IEC	Rooftop	1715	7
Minnesota	2015	Colocation	Oasis IEC	Rooftop	1455	5
British Columbia, Canada	2015	Colocation	Oasis IEC	Rooftop	195	1
Pennsylvania	2015	Enterprise	Oasis IEC	Rooftop	2235	5
British Columbia, Canada	2015	Enterprise	Oasis IEC	Rooftop	125	2
British Columbia, Canada	2015	Enterprise	Oasis IEC	Outside Perimeter on Concrete pad	60	1
Alberta, Canada	2015	Colocation	Oasis IEC	Outside Perimeter on Concrete pad	1375	5
Alberta, Canada	2015	Colocation	Oasis IEC	Outside Perimeter on Concrete pad	1925	7
Washington	2015	Colocation	Oasis IEC	Rooftop	1914	7
North Carolina	2015	Enterprise	Oasis IEC	Outside Perimeter on Concrete pad	7740	18
Massachusetts	2015	Colocation	Oasis IEC	Rooftop	1520	4
British Columbia, Canada	2014	Enterprise	Oasis IEC	Indoors along perimeter	69	3
Nevada	2014	Enterprise	Oasis DEC	Outside Perimeter on Concrete pad	125	1
Washington	2014	Colocation	Oasis IEC	Indoors along perimeter	2138	60
Utah	2014	Enterprise	Oasis IEC	Rooftop	1575	7
North Carolina	2014	Enterprise	Oasis IEC	Outside Perimeter on Concrete pad	2340	9
New Jersey	2014	Colocation	Oasis IEC	Rooftop	4008	12
Washington	2014	Colocation	Oasis IEC	Rooftop	2476	10
Oregon	2014	Colocation	Oasis IEC	Rooftop	1367	4
Washington	2014	Colocation	Oasis IEC	Rooftop	800	4
Alberta, Canada	2014	Colocation	Oasis IEC	Outside Perimeter on Steel Dunnage	500	2

Project Location	Installed	Customer	Product Description	Equipment Location	IT Cooling load kW	Qty
AMER cont...						
Alberta, Canada	2014	Colocation	Oasis IEC	Outside Perimeter on Steel Dunnage	750	3
Alberta, Canada	2013	Colocation	Oasis IEC	Indoors along perimeter	1320	6
Ontario, Canada	2013	Colocation	Oasis IEC	Indoors along perimeter	1320	6
California	2013	Colocation	Oasis IEC	Rooftop	900	3
Alberta, Canada	2013	Colocation	Oasis IEC	Outside Perimeter on Steel Dunnage	500	2
Washington	2013	Colocation	Oasis IEC	Rooftop	200	1
Nevada	2013	Enterprise	Oasis DEC	Outside Perimeter on Concrete pad	1220	8
Oregon	2013	Enterprise	Oasis IEC	Rooftop	2360	10
Alberta, Canada	2013	Colocation	Oasis IEC	Indoors along perimeter	1440	6
California	2012	Colocation	Oasis IEC	Rooftop	6260	13
Alberta, Canada	2012	Colocation	Oasis IEC	Outside Perimeter on Steel Dunnage	750	3
Jalisco, MEX	2012	Enterprise	Oasis IEC	Rooftop	2250	17
Oregon	2012	Enterprise	Oasis IEC	Rooftop	1340	6
Oregon	2012	Enterprise	Oasis IEC	Rooftop	5030	18
Michigan	2012	Enterprise	Oasis IEC	Outdoor Perimeter on Steel Dunnage	600	4
Washington	2012	Colocation	Oasis IEC	Indoors along perimeter	1140	32
Various	2011-2013	Various	Oasis DEC	Internal to AHU or part of field built system	5800	0
Nevada	2011	Enterprise	Oasis IEC	Outside Perimeter on Steel Dunnage	750	3
Washington	2011	Colocation	IASE	Rooftop	9900	22
Washington	2011	Colocation	Oasis IEC	Rooftop	2000	12
Washington	2011	Colocation	Oasis IEC	Rooftop	2700	12
California	2011	Enterprise	Oasis IEC	Rooftop	1620	6
Washington	2011	Enterprise	Oasis DEC	Indoors along perimeter	11300	36
Nebraska	2011	Enterprise	Oasis DEC	Outside Perimeter on Concrete pad	1700	2
New York	2010	Enterprise	Oasis DEC	Indoors along perimeter	14400	45
					165355	616

EMEA						
Milan, Italy	2017	Colocation	Oasis IEC	Outside Perimeter on Steel Dunnage	1600	5
Ireland	2016	CONFIDENTIAL	Oasis IEC	Rooftop	30000	132
Ireland	2016	CONFIDENTIAL	Oasis IEC	Rooftop	30000	132
Milan, Italy	2016	Colocation	Oasis IEC	Perimeter	2500	9
Milan, Italy	2016	Colocation	Oasis IEC	Outside Perimeter on Steel Dunnage	3000	9
London UK	2016	Colocation	Oasis IEC	Indoor Plant Area	8000	40
Stockholm, Sweden	2016	Colocation	Oasis IEC	Rooftop	400	4
Stockholm, Sweden	2015	Colocation	Oasis IEC	Rooftop	550	6
Oslo, Norway	2013-2015	Colocation	Oasis IEC	Indoors along perimeter	9800	49
Birmingham, UK	2015	Enterprise	Oasis IEC	Outside Perimeter on Concrete pad	250	3
Milan, Italy	2015	Colocation	Oasis IEC	Outside Perimeter on Concrete pad	400	4
Saarbrücken, Germany	2015	Colocation	Oasis IEC	Rooftop	1500	8
Hofkirchen, Germany	2015	Colocation	Oasis IEC	Outside Perimeter on Concrete pad	400	2
Antwerp Belgium	2014	Colocation	Oasis IEC	Outside Perimeter on Concrete pad	200	2
London, UK	2014	Colocation	Oasis IEC	Indoor plant area	8000	40
Dublin, Ireland	2014	Colocation	Oasis IEC	Outside Perimeter on Concrete pad	800	4
Oostkamp, Belgium	2011-2014	Colocation	Oasis IEC	Outside Perimeter on Concrete pad	600	3
Gent, Belgium	2013	Colocation	Oasis IEC	Outside Perimeter on Concrete pad	400	2
Vilnius, Lithuania	2013	Colocation	Oasis IEC	Outside Perimeter on Concrete pad	250	2
Coleraine, NI	2013	Enterprise	Oasis IEC	Outside Perimeter on Concrete pad	190	2

Project Location	Installed	Customer	Product Description	Equipment Location	IT Cooling load kW	Qty
------------------	-----------	----------	---------------------	--------------------	--------------------	-----

EMEA cont...

Inverno, Italy	2012	Colocation	Oasis IEC	Outdoor Perimeter on Steel Dunnage	900	7
Milan, Italy	2016	Colocation	Oasis IEC	Outside Perimeter on Steel Dunnage	3000	9
Milan, Italy	2017	Colocation	Oasis IEC	Outside Perimeter on Steel Dunnage	1600	5
Dublin, Ireland	2017	Digital	Oasis DEC	Internal to AHU or part of field built system	48000	74
Amsterdam, Netherlands	2016	Digital	Oasis DEC	Internal to AHU or part of field built system	65000	160
Dublin, Ireland	2016	Digital	Oasis DEC	Internal to AHU or part of field built system	11550	47
Dublin, Ireland	2016	Digital	Oasis DEC	Internal to AHU or part of field built system	48000	74
Dublin, Ireland	2016	Digital	Oasis DEC	Internal to AHU or part of field built system	48000	74
Dublin, Ireland	2016	Digital	Oasis DEC	Internal to AHU or part of field built system	48000	74
Dublin, Ireland	2016	Digital	Oasis DEC	Internal to AHU or part of field built system	48000	74
Dublin, Ireland	2014	Enterprise	CRAH	Internal to AHU or part of field built system	22400	80
Dublin, Ireland	2014	Enterprise	CRAH	Internal to AHU or part of field built system	69440	248
Dublin, Ireland	2014	Enterprise	CRAH	Internal to AHU or part of field built system	109200	390
Brussels, Belgium	2014	Enterprise	Oasis DEC	Rooftop	2600	12
Amsterdam, Netherlands	2014	Enterprise	Oasis DEC	Internal to AHU or part of field built system	6500	160
Sarl, Switzerland	2011	Enterprise	Oasis DEC	Indoors along perimeter	5120	16
					636150	1962

APAC

Tokyo, Japan	2016	Enterprise	Oasis IEC	Outdoor	2000	12
Melbourne, Australia	Q4 2015	Colocation	Oasis IEC	Indoors along perimeter	2100	20
Sydney, Australia	2015	Colocation	Oasis IEC	Indoor plant area	4200	24
Melbourne, Australia	2014	Colocation	Oasis IEC	Indoors along perimeter	1000	10
Tsukuba, Japan	2012	University	Oasis IEC	Outdoor	200	1
Sydney, Australia	2011	Colocation	Oasis IEC	Rooftop	4000	44
					49500	111
*IEC= Indirect Evaporative Cooler *DEC = Direct evaporative Cooler *CRAH = Computer Room Air Handling Unit			Total MW 851,00		851005	2689

Australia Phone +61 2 8843 1588, dh.info@munters.com.au Austria Phone +43 1 6164298-0, luftentfeuchtung@munters.at Belgium Phone +32 1528 5611, info@muntersbelgium.be Brazil Phone +55 41 3317 5050, munters@com.br Canada Phone +1 905 858 5894, dhinfo@munters.com China Phone +86 10 8041 8000, info@munters.com.cn Czech Republic Phone +420 544 211 434, info@munters-odvlhcovani.cz Denmark Phone +45 4495 3355, info@munters.dk Finland Phone +358 20 776 8230, laitemynti@munters.fi France Phone +33 1 3411 5757, dh@munters.fr Germany Phone +49 4087 96900, mgd@munters.de India Phone +91 20 668 18 900, info@munters.in Italy Phone +39 0183 52 11, marketing@munters.it Japan Phone +81 3 5970 0021, mkk@munters.co.jp Korea Phone +82 2761 8701, munters@munters.co.kr Mexico Phone +52 722 270 40 49, munters@munters.com.mx Netherlands Phone +31 172 433231, vachtbeheersing@munters.nl Poland Phone +48 58305 3517, dh@munters.pl Singapore Phone +65 6744 6828, info@munters.com.sg South Africa Phone +27 11 997 2000, info@munters.co.za Spain Phone +34 91 640 09 02, marketing@munters.es Sweden Phone +46 8 626 63 00, avfukning@munters.se Switzerland Phone +41 52 343 8886, info.dh@munters.ch Thailand Phone +66 2642 2670, info@munters.co.th Turkey Phone +90 216 548 1444, info@muntersform.com UAE +971 4887 6462, middle.east@munters.com United Kingdom Phone +44 1480 432243, info@munters.co.uk USA Phone +1 978 241 1100, dhinfo@munters.com Vietnam Phone +84 8 8256 838, vietnam@muntersasia.com



Global Enquires to:
datacentres@munters.com
munters.com/datacentres

+44 1480 410223