



- B1 Safety thermostat
- G1 Gas valve
- M1 Fan motor
- Q1 Switch
- Q2 Piezoelectric ignition
- Q3 Phase transformer
- S1 Ignition electrode
- S2 Thermocouple
- Y1 Solenoid valve

00	02/12/2009	First issue (era dis. E0050001 - cod. 1014037555 poi 1105047955)	D. Fulcheri
Rev.No	Date	Description	Drawer
Linear dimension range	up to 6	over 6 up to 30	over 30 up to 120
tolerance limits	±0.3	±0.5	±0.8
		±1.2	±2
		±3	±4

Description		Schema elettrico KID 30-40 MV e ARG 35 MV		Drawing No	SCH089
		Wiring diagram KID 30-40 MV - ARG 35 MV		File name	SCH08900
Material	-	Thickness	- mm	Drawer	P.A. Cda
		Weight	- g	Latest revision approved by	V. Sanna
 MUNTERS ITALY S.p.A. - Mondovì This drawing is exclusive property of MUNTERS ITALY S.p.A.. Any violation, reproduction or release without written authorization by MUNTERS ITALY S.p.A. is ABSOLUTELY FORBIDDEN		Drawing scale	-	Date	23/01/1998
		DIMENSIONS WITHOUT TOLERANCE LIMITS: ROUGH PRECISION LEVEL UNI EN 22768-1/2		Manufactured part No	20290272