

Product Information
Natural Center / Natural Master

- Maximum and minimum ventilation level according to outside temperature
- Differentiated target temperature settings for day and night time
- Control, Management and History features
- Regulates up to 10 units
- Manages an entire network from a single computer
- Has a user-friendly programming interface
- Sends alarms alerting you of any problem

Natural Center / Natural Master

Munters advanced Natural Center and Natural Master climate controllers are two innovative products that work together to facilitate ease of operation and trouble free climate control.

The user-friendly Munters solution is based on an inclusive system, in which one central server – Natural Center controls high-performance Natural Master control units which can be installed in the different areas of the facility. Up to 10 Master units can be connected to 1 Center unit.

By choosing the Natural Center and Natural Master control system, you obtain a wide range of monitoring options and automated ventilation adjustments in accordance with your requirements. By ensuring ideal natural ventilation for your barn/stable, you greatly increase the livestock welfare and thereby your production yield. Munters Natural Center and Natural Master controllers provides an excellent combination of ventilation control, adjustment and monitoring and forms an integral part of the natural ventilation for livestock stables and milking parlours.

Rugged and weather proof control boxes are designed for fast access to adjust ventilation and offers user friendly interface menu for the operator.



Weather station application



The weather station (installed on the ridge of the stable) provides information on wind speed, direction as well as precipitation. Controllers can be set to close curtains (or ridge vent) completely or gradually if it starts to rain or if the wind conditions change.

Natural Master / Natural Center controllers are developed and produced by Munters A/S, Denmark

Australia Phone + 61 2 8843 1588, dh.info@munters.com.au, **Brazil** Phone +55 41 3317 5050, contato@munters.com, **Canada** Phone +1 517 676 7070, aghort.info@munters.com, **China** Phone +86 10 8048 3493, marketing@munters.cn, **Denmark** Phone +45 98 623 311, aghort@munters.dk, **India** Phone +91 20 6681 8900, info@munters.in, **Indonesia** Phone +66 2 642 2670, info@munters.co.th, **Italy** Phone +39 0183 5211, info@munters.it, **Japan** Phone +81 3 5970 0021, mkk@munters.jp, **Korea** Phone +82 2 7618 701, munters@munters.co.kr, **Mexico** Phone +52 818 2625 400, dhinfo@munters.com, **Singapore** Phone +65 7 446 828, info@munters.com.sg, **South Africa and Sub-Sahara Countries** Phone +27 11 997 2000, info@munters.co.za, **Spain** Phone +39 0183 5211, info@munters.it, **Sweden** Phone +46 8 6266 300, info@munters.se, **Thailand** Phone +66 2 6422 670, info@munters.co.th, **Turkey** Phone +90 262 7513 750, info@muntersform.com, **USA** Phone +1 517 676 7070, aghort.info@munters.com, **Export & Other countries** Phone +39 0183 5211, info@munters.it



Munters

Your closest distributor