

TEMPERATURE SENSOR

P/N: 918-01-00001



Specifications

- **Type :** 30 Kohm Thermistor
- **Maximum Cable Length:** 500 meter (1640 feet)
- **Curve Number:** 1
- **Typical Accuracy:** 0.3° C
- **Maximum 25°C Tolerance:** ±3%
- **Operating Temperature:** -40° to 105° C / -40° to 221° F
- **Maximum Cable Length:** 500 meter
- **Minimum wire size:** 22 AWG (2 wire shielded cable)

TEMPERATURE SENSOR

P/N: 918-01-00001



Specifications

- **Type :** 30 Kohm Thermistor
- **Maximum Cable Length:** 500 meter (1640 feet)
- **Curve Number:** 1
- **Typical Accuracy:** 0.3° C
- **Maximum 25°C Tolerance:** ±3%
- **Operating Temperature:** -40° to 105° C / -40° to 221° F
- **Maximum Cable Length:** 500 meter
- **Minimum wire size:** 22 AWG (2 wire shielded cable)