

Product sheet
Vario

- Built with thermally insulated polyurethane material and premium corrosion resistant materials to assure top performance for many years.
- Diameter of 36 inches.
- Adjustable air distribution across a large distribution diameter.
- Variable speed option available.
- Mounts to ceiling using chain links.



VARIO © Copyright Munters Corporation 2017

Vario

Engineered to mix large volumes of air and provide even temperatures throughout your facility. Made from thermally insulated polyurethane material and built with premium corrosion resistant materials to assure top performance for many years. Ideally suited for new, large cage-free buildings.

Uses a quiet 36 inch variable speed fan that can keep precise control over air flow. Fan may be customized to fit the application and seasonal needs. Fan performance is 12,450 cfm and throws air up to 72 feet.

The Vario sliding fan module makes it possible to variably adjust the volume vs. throw output. Vario is designed specifically for 100% of fan output available as recirculated air during operation. Used with the BI28 Ceiling Inlet and Professional 2900 Sidewall Inlet to add fresh air and maintain the correct amount of fresh air and circulated air to keep your building's climate stable.



Technical Information

Interior Diameter		Air Flow	
inch	millimeter	cfm	[m ³ /h]
36	920	12,450	21,125

NOTE:




Variable Up/Down 0" – 12" Max Open

The sliding fan module on the Vario makes it possible to variably modify the recirculation gap.

Throwing Range*

Up to 72 feet.

Planning starts with an even distribution of the Vario fans. Near equal sized areas ensure an optimum distribution of fresh air. The fresh air distributor can be employed in equal pressure systems.



*Dependant on pressure, outside temperature and internal stable temperature.



Australia Munters Pty Limited, Phone +61 2 8843 1594, **Brazil** Munters Brasil Industria e Comercio Ltda, Phone +55 41 3317 5050, **Canada** Munters Corporation Mason, Phone +1 517 676 7070, **China** Munters Air Treatment Equipment (Beijing) Co. Ltd, Phone +86 10 80 418 000, **Denmark** Munters A/S, Phone +45 9862 3311, **India** Munters India, Phone +91 20 6681 8900, **Indonesia** Munters, Phone +62 818 739 235, **Italy** Munters Italy S.p.A., Chiusavecchia, Phone +39 0183 52 11, **Japan** Munters K.K., Phone +81 3 5970 0021, **Korea** Munters Korea Co. Ltd., Phone +82 2 761 8701, **Mexico** Munters Mexico, Phone +52 818 262 54 00, **Russia** Munters AB, Phone +7 812 448 5740, **Singapore** Munters Pte Ltd., Phone +65 744 6828, **South Africa and Sub-Sahara Countries** Munters (Pty) Ltd., Phone +27 11 997 2000, **Spain** Munters Spain S.A., Phone +34 91 640 09 02, **Sweden** Munters AB, Phone +46 8 626 63 00, **Thailand** Munters Co. Ltd., Phone +66 2 642 2670, **Turkey** Munters Form Endüstri Sistemleri A.Ş, Phone +90 262 751 3750, **USA** Munters Corporation Lansing, Phone +1 800 227 2376, **Vietnam** Munters Vietnam, Phone +84 8 3825 6838, **Export & Other countries** Munters Italy S.p.A., Chiusavecchia Phone +39 0183 52 11.

Your closest distributor

Munters reserves the right to make alterations to specifications, quantities, etc., for production or other reasons, subsequent to publication.

© Munters Corporation 2017