



Product Information
MTC: Munters Topfixated Curtain

- Curtain protects against wind and severe weather conditions
- Variable opening
- Curtain opens from bottom and up
- Manufactured in UV resistant PVC coated high tenacity polyester
- Anti-static treatment repels dirt (straw, sand, dust)
- "Click & Go" wind pipes enabling vehicular access directly into shed
- Optimal light transmission

MTC: Munters Topfixated Curtain

Munters Topfixated Curtain is typically installed in livestock installations, where the need for regulation of the opening area is limited also the curtain is manually adjustable (electric).

The curtain rolls from the bottom and up which make access to the stable easier for example in connection with cleaning or the like.

The simple design where only the bottom profile is the moving part and the top of the curtain is fixed to the construction of the house makes installation, connection, service and use of the curtain very simple and straightforward.

Munters A/S,

Nordvestvej, 3 - 9600 Aars, Denmark / Phone +45 986 233 11 / Fax +45 986 213 54 / www.munters.dk/agro



Product description

The Munters Topfixated Curtain is manufactured in heavy duty, UV resistant PVC coated high tenacity polyester. The light grey color ensures optimal light transmission. The curtain is anti-static and will repel dirt (sand, straw, dust). The curtain rolls on an extruded aluminum profile.

As safety against strong winds, specially designed wind pipes are installed at intervals of 2 meters (recommended distance – distance varies depending on opening height). The wind pipes are made of galvanized iron with an outer plastic pipe – the latter to minimize wear and tear on both wind pipe and curtain. Wind pipes are installed on the outside and inside of the curtain, acting as a guide for the curtain.

In cases where an even wider access into the shed is required (wider than the recommended 2 m distance between the wind pipes), the MTC curtain can be delivered with detachable wind pipes - the so-called "Click & Go" solution. With "Click & Go", the wind pipes are easily "clicked out" from their normal position between the steel trusses on the building – thus enabling a wider access.

Technical data

Max height	4 meter
Max length	100 meter (maximum 300 m ² per section)
Power	3 phase 400V
Function	Roll from the bottom up
Accessories	Removable windpipes



Australien Munters Pty Limited, Phone +61 2 8843 1594, **Brasilien** Munters Brasil Industria e Comercio Ltda, Phone +55 41 3317 5050, **Canada** Munters Corporation Mason, Phone +1 517 676 7070, **Kina** Munters Air Treatment Equipment (Beijing) Co. Ltd, Phone +86 10 80 418 000, **Denmark** Munters A/S, Phone +45 9862 3311, **India** Munters India, Phone +91 20 3052 2520, **Indonesien** Munters, Phone +62 818 739 235, **Italien** Munters Italy S.p.A., Chiusavecchia, Phone +39 0183 52 11, **Japan** Munters K.K., Phone +81 3 5970 0021, **Korea** Munters Korea Co. Ltd., Phone +82 2 761 8701, **Mexico** Munters Mexico, Phone +52 818 262 54 00, **Singapore** Munters Pte Ltd., Phone +65 744 6828, **Sydafrika & landene syd for Sahara** Munters (Pty) Ltd., Phone +27 11 997 2000, **Spanien** Munters Spain S.A., Phone +34 91 640 09 02, **Sverige** Munters AB, Phone +46 8 626 63 00, **Thailand** Munters Co. Ltd., Phone +66 2 642 2670, **Tyrkiet** Munters Form Endüstri Sistemleri A.Ş, Phone +90 262 751 3750, **USA** Munters Corporation Mason, Phone +1 517 676 7070, **Vietnam** Munters Vietnam, Phone +84 8 3825 6838, **Export & other countries** Munters Italy S.p.A., Chiusavecchia Tlf. +39 0183 52 11

Munters reserves the right to make alterations to specifications, quantities, etc., for production or other reasons, subsequent to publication.

© Munters, 2015

Your closest distributor