



ML Series with Climatix MLT30 Desiccant dehumidifier

Features

- Modern Climatix control system
- Small footprint requires minimal floor area
- High airflow capacity
- Minimal energy consumption
- Unique plastic rotor casing
- 100% corrosion resistance
- Dehumidifies efficient down to -20 C
- Communication and external control options

MLT30 with Climatix

The MLT30 desiccant dehumidifier with climatix control is designed to efficiently dehumidify in low moisture applications.

It is equipped with an internally sealed rotor unit. The rotor casing is constructed of durable thermoset plastic and contains isolated sections that provide a precise balance for dehumidification, reactivation, and heat recovery airflows. Its rugged formed metal frame and access panels are produced from corrosion resistant Aluzink®. MLT30 can be delivered with 3 different reactivation alternatives – electricity, steam or gas.

The modern control system conforms to EN 60204 (IEC204) standards and is equipped with a number of alarm functions to ensure total control of the dehumidification process.


ML Series dehumidifiers conform to both harmonised European Standards and to CE marking specifications.



ML with Climatix Controls

Model MLT30 with Climatix

Measurement diagram for reference only




Width A	Depth B	Height C	Diam. D	Diam. E	Weight
1200mm	870mm	1790mm	315mm	200mm	305kg

Technical Specification

Process Air		Miscellaneous Data	
Rated airflow (m ³ /h)	3000	Operating temperature (°C)	-20/+40
Available static pressure (pa)	300	Sound power level to room Lw(A) dB, all inlets and outlets ducted	76
		Air filter standard	G3
Reactivation air		IEC protective class (unit)	IP33
Rated airflow (m ³ /h)	630	IEC protective class (electrical)	IP44
Available static pressure (pa)	300		
Total Power Voltage & Current (amps & phase)			
Total power (kW) Electrical	22,0(50Hz)		
Total power (kW) Electrical	22,6 (60Hz)		
Total power (kW) Steam/Gas	4,0(50Hz)		
Total power (kW) Steam/Gas	4,6(60Hz)		
230V 3-50Hz (A) Electrical	60,1		
230V 3-50Hz (A) Steam/Gas	15,8		
380V 3-50Hz (A) Electrical	36,4		
380V 3-50Hz (A) Steam/Gas	10,0		
400V 3-50Hz (A) Electrical	35,1		
400V 3-50Hz (A) Steam/Gas	10,0		
415V 3-50Hz (A) Electrical	34,0		
415V 3-50Hz (A) Steam/Gas	10,0		
440V 3-60Hz (A) Electrical	32,6		
440V 3-60Hz (A) Steam/Gas	9,9		
460V 3-60Hz (A) Electrical	31,6		
460V 3-60Hz (A) Steam/Gas	9,9		
480V 3-60Hz (A) Electrical	30,6		
480V 3-60Hz (A) Steam/Gas	9,9		
Steam consumption (g/s) at 4 bar (g)	9		

Dehumidification Capacity



Options

- Communication via Modbus, BACnet
- Dewpoint sensor
- External controls
- External Filter Box M5 or F7
- Heaters-gas, electric or steam
- Insulated process air inlet
- Mirror handed
- Stainless steel casing



For more information visit munters.com



Australia Phone +61 2 8843 1588, dh.info@munters.com.au Austria Phone +43 1 6164298-92-51, luftentfeuchtung@munters.at Belgium Phone +32 1528 5611, info@muntersbelgium.be Brazil Phone +55 41 3317 5050, munters@com.br Canada Phone +1 905 564 6466, dhinfo@munters.com China Phone +86 10 8048 3493, info@munters.com.cn Czech Republic Phone +420 775 569 657, info@munters-odvlhcovani.cz Denmark Phone +45 4495 3355, info@munters.dk Finland Phone +358 20 776 8230, laitemyynti@munters.fi France Phone +33 1 3411 5757, dh@munters.fr Germany Phone +49 4087 96900, mgd@munters.de India Phone +91 20 668 18 900, info@munters.in Italy Phone +39 0183 52 11, marketing@munters.it Japan Phone +81 3 5970 0021, mkk@munters.co.jp Korea +82 2761 8701, munters@munters.co.kr Mexico Phone +52 81 8262 5400, munters@munters.com.mx Netherlands Phone +31 172 433231, vochtbeheersing@munters.nl Poland Phone +48 58305 3517, dh@munters.pl Singapore Phone +65 6744 6828, info@munters.com.sg South Africa Phone +27 11 997 2000, info@munters.co.za Spain Phone +34 91 640 09 02, marketing@munters.es Sweden Phone +46 8 626 63 00, avfuktning@munters.se Switzerland Phone +41 52 343 8886, info.dh@munters.ch Thailand Phone +66 2642 2670, info@munters.co.th Turkey Phone +90 262 751 3750, info@muntersform.com UAE +971 4 8809295, middle.east@munters.com United Kingdom Phone +44 1480 432 243, dryair@munters.co.uk USA Phone +1 978 241 1100, dhinfo@munters.com Vietnam Phone +84 8 8256 838, vietnam@muntersasia.com