



Item	Catalog No.		Part Name/Description	Qty
	54GC	54GCX		
1	FH1255	FH1255	Orifice Panel, GZ	1
2	FH2972	FH2972	Top housing panel, with shutter clips, GZ	1
3	FH2970	FH2970	Right side housing panel, with shutter clip, GZ	1
4	FH2973	FH2973	Bottom housing panel, with shutter clips, GZ	1
5	FH2971	FH2971	Left side panel of housing, with shutter clip, GZ	1
6	FP1454	FP1454	Propeller assembly, 3-blade, GZ	1
7	FH2429	FH2429	Support bracket for motor mounting plate, GZ	1
8	FH2427	FH2427	Mounting plate for NEMA 56 motor, GZ	1
9	FH2428	FH2428	Brace for Strut, GZ	1
10	FM1046*	FM1046*	Motor, 1.5HP, 1725 RPM, 56Fr., 1ph, 120/240	1
11	FH1302	FH1302	Reinforcement bracket for strut, GZ	2
12	KN1860	KN1860	Hex nut, M25x10mm, ZP	1
13	KX1208	KX1208	Cover for hex nut, black plastic	1
14	FH1929	FH1929	Center Strut, GZ	1
15	FH1932	FH1932	Spacer plate, black plastic	2
16	FH1514*	FH1514*	V-belt, 93" A-section aramid fiber, AP91	1
17	KX1130	KX1130	Shaft shield, AL	1
18	FH2137*	FH2137*	Propeller sheave, AL	1
19	FP2060	FP2060	Hub with bearing and shaft	1
20	FH2504	FH2504	Mounting bracket for belt tensioner	1
21	FH2402K	FH2402K	Belt tensioner assembly with 3" idler pulley	1
	FH2406	FH2406	3" idler pulley only, with bolt	1
	FH2439	FH2439	Tensioner arm only, AL	1
22	FH1996*	FH1996*	Motor Sheave AK43 x 5/8" bore for 1.5 HP fans	1
23	FH2130	FH2130	Cone support bracket, GZ	4
24	FH4254	FH4354	Top/bottom cone section, GZ	2
25	FH4257	FH4454	Side cone section, GZ	2
26	-	KX1256	1"L, black plastic	10
27	FH2654	FH2654	Guard, Flat sided cone, 1/2 circle PVC coated	2
28	PZ54 or GS54	PZ54 or GS54	Shutter, 55 ⁵ / ₈ "W. x 60 ¹ / ₈ "H., all plastic or aluminum blade/galvanized frame	1

* Parts listed are for standard configuration with 1.5 HP motor and other drive components operating on 60Hz power. Contact office for other configurations.