



Item	Catalog No.	Description	Qty.
1	JP3028	8" Pipe (SDR81) with Cut Lines, PVC	varies/foot
2	EC1328	Pipe Support Bracket, without Holes, AL	varies/foot
3	EC1330	Pipe Support Bracket, with Holes, AL	varies/foot
4	KS2105	#14 x 1 1/2" Lag Screw, SS	varies
5	KS2462	3/8" x 3 1/2" Lag Screw, HOT DIP GALV.	varies
6	KS2257	#10 x 1 1/4" TEK Screw, ZP	varies
7	EC1340	Drip Collector Splice, 6"W., PL	varies
8	EC1290	Drip Collector, 2'L., White PVC	varies
	EC1291	Drip Collector, 4'L., White PVC	varies
	EC1296	Drip Collector, 5'L., White PVC	varies
	EC1294	Drip Collector, 10'L., White PVC	varies
9	EC1148	1" x 3/4" Drain Fitting, PVC	varies
10*	CEL1545061272M1	CELdek® Pad Material	varies
11	EC1081	End Panel, 83.25"H., PL	2
12	EC1310	Drip Collector End Cap, PL	2
13	EC1299	1 1/2" x 10"L. Pipe Nipple, SDR21, PVC	2
14	EC1224	1 1/2" Ball Valve, Schedule 40, PVC	1
15	EC1498	Pipe, 1.5"D x 10'-2.5"L., w/Holes: 1/8"D., 3"O.C., Bell, PVC	varies
16	KN2302	5/16"-18 Wing Nut, Type-A, NY, Black Color	varies
17	KS1009	5/16"-18 x 6" Hex Bolt, SS	varies
18	EC1031	Pipe Holder for 1 1/2" Dia. Pipe, AL	varies
19	EC1226	1 1/2" Slip Cap, Schedule 40, PVC	1
20	KS2257	#10 x 1 1/4" TEK Screw, ZP	varies
21	EC1078	Distribution Cap, 2'L., AL	varies/foot
	EC1072	Distribution Cap, 4'L., AL	varies/foot
	EC1079	Distribution Cap, 5'L., AL	varies/foot
	EC1076	Distribution Cap, 10'L., AL	varies/foot
22	EC1202	Angle Bracket, 1 1/2" x 4" x 1 1/2", AL	2
23	Standard Pad Retainer		
	EC1071	Pad Retainer, 2'L., AL	varies/foot
	EC1065	Pad Retainer, 4'L., AL	varies/foot
	EC1070	Pad Retainer, 5'L., AL	varies/foot
	EC1068	Pad Retainer, 10'L., AL	varies/foot
	OPTIONAL: Open Header Pad Retainer		
	EC1902	Pad Retainer, Open Style, 2'L., AL	varies/foot
	EC1904	Pad Retainer, Open Style, 4'L., AL	varies/foot
	EC1905	Pad Retainer, Open Style, 5'L., AL	varies/foot
	EC1910	Pad Retainer, Open Style, 10'L., AL	varies/foot

* Catalog Number changes depending on type and size of pad.