



Spare Parts List

M120



Desiccant dehumidifier



Assy	Item	PartNo	Description	Specification	Qty
CA	2	19013535	Spring		4
CA	2	19013569	Washer		4
CA	2	19023050	Retainer clip		4
CA	3	19022964	Impeller react.		1
CA	4	19022935	Fan back plate		1
CA	7	19017019	Rotor HPS		1
CA	7	19013571	Gear ring		1
CA	8	19022967	Impeller process		1

A	1	19013547KIT	Filter		1
A	2	190180000-1	PCB 200/230V		1
A	2	190180000-2	PCB 115V		1
A	3	19013551	Seal		1
A	8	19022939	Gable dry air side		1
A	9	19013548	Filter cover	Reactivation	1
A	10	19013550	Cover plate		1
A	11	19013560	Blind plug		1
A	12	19020905	Reset button		1
A	13	19013204	Grommet		1
A	14	19022937-01	Silicon tube	D=6.5mm L=800mm	1
A	15	19013546	Fan inlet		1
A	16	19013208	Plug		1
A	17	19013565	Orifice plate 50Hz		1
A	17	19013566	Orifice plate 60Hz		1
A	18	19024039E	Humidistat connection kit		1
B	1	19013529KIT	Heater unit 115V		1
B	1	1700256-200	Heater unit 200V		1
B	1	19013497	Heater unit 230V		1
B	2	19022933	Pressure plate		1
B	3	19024917E	Thermostat		1
B	5	19013204	Grommet		1
B	6	19016706	Gasket		1
B	7	1505966-01	Slide bearing		4
C	1	19022931E	Casing		1
C	2	170-032346-003	Fan motor kit 115V	with capacitor	1
C	2	19030106	Fan motor 200V		1
C	2	170-032346-001	Fan motor kit 230V	with capacitor	1
C	5	19013573	Bearing		3
C	9	19016728	Plug		2
C	10	19022936	O-ring		1
C	12	19023047	Spindle		4
C	14	19016706	Gasket		1
D	1	19022938	Gable wet air side		1
D	3	19013547KIT	Filter		1
D	4	19013546	Fan inlet		1
D	5	19013549	Filter cover	Process	1
E	1	19022921	Bracket		1
E	2	19023036	Plate, decal		1
E	5	150-032347-001	Capacitor 2.5μF	For 230V SIMEL fan motor	1
E	5	150-016156-001	Capacitor 2μF	For 230V ATB fan motor	1
E	5	150-016156-001	Capacitor 2μF	For 200V fan motor	1
E	5	150-032347-003	Capacitor 10μF	For 115V SIMEL fan motor	1
E	5	150-016161-001	Capacitor 8μF	For 115V ATB fan motor	1
E	6	19022932E	Guide washer		1

E	8	19013570	Pinion	incl. Screw	1
E	10	170-019440-001	Drive motor 200/230V		1
E	10	170-019442-001	Drive motor 115V		1
E	11	1505842-01	Capacitor 0.12µF	For 200/230V	1
E	11	1505860-01	Capacitor 0.5µF	For 115V	1

PEN-M120-C1910

www.munters.com