

Product Information

Ridge ventilation, aluminium - fixed or adjustable opening


- Ideal combination of natural ventilation and optimum light dispersion in any form of barn/stable
- Rigid, weather proof construction, designed to withstand the climate conditions in northern Europe
- Double walled, 10 mm, UV resistant Lexan PC (PolyCarbonate) sheet material with 10 years limited warranty on light transmission
- Optimal transparency
- Wind deflectors made from corrugated metal sheets prevent rain, snow, hail and dirt from entering the barn/stable
- Wind deflectors can be equipped with a manual or automatic closing system to seal of the barn/stable during extreme weather conditions
- Varying height and width to accommodate individual requirements for air capacity and light dispersion
- The ridge vent is part of the emergency ventilation in case of fire




Ridge ventilation, aluminium with fixed or adjustable opening

By choosing the ideal solution to provide natural ventilation for your barn/stable, you greatly increase the livestock welfare and thereby your production yield. Munters ridge ventilation, aluminium provides an excellent combination of ventilation and light dispersion as an integral part of the natural ventilation for livestock barns and stables.

The ridge can replace part of the roof, mounted with either fixed or adjustable opening. If the Ridge ventilation mounted with adjustable opening, the opening can be operated by a damper motor or manual winch. Both versions can be equipped with a Bird net.





Insulated and UV resistant Lexan PC (PolyCarbonate) sheets ensure little or no condensation on the inside of the structure. The sheet profile and technical specification provides a rugged and weather proof solution with optimum translucency, performance and ease of operation. The width of the ridge is produced by request from 1 m. up to 4 m. Munters ridge ventilation, aluminium can be controlled automatically by NaturalCenter / NaturalMaster with temperature sensor and weather station with wind- and rain sensor, which provides the optimal climate control for the stable doing all weather conditions.

The designs of the ridge vent and wind deflector results in a vacuum effect, which effectively sucks out the warm and stale air inside the barn/stable. By choosing the dynamic wind deflector solution, you enhance your climate control options, manually or automatically, to provide additional protection of your livestock during the times of year with extreme weather conditions.



Australia Phone + 61 2 8843 1588, dh.info@munters.com.au, **Brazil** Phone +55 41 3317 5050, contato@munters.com, **Canada** Phone +1 517 676 7070, aghort@munters.com, **China** Phone +86 10 8048 3493, marketing@munters.cn, **Denmark** Phone +45 98 623 311, aghort@munters.dk, **India** Phone +91 20 6681 8900, info@munters.in, **Indonesia** Phone +66 2 642 2670, info@munters.co.th, **Italy** Phone +39 0183 5211, info@munters.it, **Japan** Phone +81 3 5970 0021, mkk@munters.jp, **Korea** Phone +82 2 7618 701, munters@munters.co.kr, **Mexico** Phone +52 818 2625 400, dinfo@munters.com, **Singapore** Phone +65 7 446 828, info@munters.com.sg, **South Africa and Sub-Sahara Countries** Phone +27 11 997 2000, info@munters.co.za, **Spain** Phone +39 0183 5211, info@munters.it, **Sweden** Phone +46 8 6266 300, info@munters.se, **Thailand** Phone +66 2 6422 670, info@munters.co.th, **Turkey** Phone +90 262 7513 750, info@muntersform.com, **USA** Phone +1 517 676 7070, aghort.info@munters.com, **Export & Other countries** Phone +39 0183 5211, info@munters.it

Munters reserves the right to make alterations to specifications, quantities, etc., for production or other reasons, subsequent to publication.

© Munters AB, 2016

Your closest distributor