



Product sheet
Hoods and Transitions

Fiberglass Pit Transition:

- 1 piece fiberglass construction.
- Totally corrosion resistant for protection from harsh environment
- Aluminum rails for easy shutter installation.

Fiberglass Riser Duct:

- Mount directly to building for removal of pit gases.
- The rugged fiberglass with noncorrosive fasteners assures long life.
- Easy mounting for 14" - 24" exhaust fans.

Fiberglass Weatherhoods:

- Fiberglass construction with stainless steel lag bolts.
- Easy installation with minimal maintenance.
- Available in 4 sizes to protect openings up to 60" square.

HT© Copyright Munters Corporation


Hoods and Transitions

Munters hoods and transitions allow you to customize your Aerotech fan for special applications and improved performance. The fiberglass pit transition is designed to remove dangerous pit gases. It can be custom fit in a concrete pit pump out. Our fiberglass riser duct can be mounted directly onto the building for removal of pit gases. The fiberglass weatherhood is ideal for exhaust fans or shutters when wind conditions reduce their effectiveness.




Fiberglass Pit Transition and Adapter


FPT, Pit Transition




24" Advantage® Fan



Flat Mount




12 degree angle




(Available in 16", 18" and 24")

Fiberglass Riser Duct




Fiberglass Weatherhood



Catalog No.	A	B	C	Framing Size (required on 3 sides)
FWH18	26"	26"	24½"	25"W. x 26"H.
FWH24	32"	32"	30½"	31"W. x 32"H.
FWH36	48"	48"	46½"	47"W. x 48"H.
FWH48	60"	60"	60½"	61"W. x 60"H.

Example Instalations



Hoods and Transitions are developed and produced by Munters Corporation, Mason Michigan USA



Your closest distributor

Australia Munters Pty Limited, Phone +61 2 8843 1594, Brazil Munters Brasil Industria e Comercio Ltda, Phone +55 41 3317 5050, Canada Munters Corporation Mason, Phone +1 517 676 7070, China Munters Air Treatment Equipment (Beijing) Co. Ltd, Phone +86 10 80 418 000, Denmark Munters A/S, Phone +45 9862 3311, India Munters India, Phone +91 20 3052 2520, Indonesia Munters, Phone +62 818 739 235, Italy Munters Italy S.p.A., Chiusavecchia, Phone +39 0183 52 11, Japan Munters K.K., Phone +81 3 5970 0021, Korea Munters Korea Co. Ltd., Phone +82 2 761 8701, Mexico Munters Mexico, Phone +52 818 262 54 00, Russia Munters AB, Phone +7 812 448 5740, Singapore Munters Pte Ltd., Phone +65 744 6828, South Africa and Sub-Sahara Countries Munters (Pty) Ltd., Phone +27 11 997 2000, Spain Munters Spain S.A., Phone +34 91 640 09 02, Sweden Munters AB, Phone +46 8 626 63 00, Thailand Munters Co. Ltd., Phone +66 2 642 2670, Turkey Munters Form Endüstri Sistemleri A.Ş, Phone +90 262 751 3750, USA Munters Corporation Mason, Phone +1 517 676 7070, Vietnam Munters Vietnam, Phone +84 8 3825 6838, Export & Other countries Munters Italy S.p.A., Chiusavecchia Phone +39 0183 52 11.

Munters reserves the right to make alterations to specifications, quantities, etc., for production or other reasons, subsequent to publication.

© Munters AB, 2013