

Product sheet
CC247 Elite Plus Control

- Munters Drive Compatible
- Large 16 line LCD screen
- 2 Box system
- Unmatched lightning protection
- Current building conditions shown on screen
- User defined hot keys
- Installer password can be set for protection
- USB jump drive to save and load settings
- Saves history menu's on USB
- Available message center
- 4 separate programs for stages 1-6
- Dusk til dawn lighting program
- Up to 18 water meters with water spill alarm
- Control 2nd room heater and fan
- Clean out mode
- Soaking timer

CC247 Elite® Copyright Munters Corporation

CC247 Elite Plus Control

The Elite Plus offers around the clock performance with the CC24-7 series. The CC24-7 Series is designed with a user friendly interface, expand ability and many other features which make it the ultimate building management tool. The Elite Plus offers a number of added benefits, including a large 16 line LCD screen, message center, programmable hot keys and much more.

This control is compatible with a variety of accessories that will further enhance your building management. Humidity sensor, static pressure module, backup relay box, water meters and Agri-Alert alarm system are a few of the accessories.



Munters Corporation, Business Area AgHort

2691 Ena Drive Lansing, MI 48917 USA / Phone: +1 517-676-7070 Fax: 517-676-7078

Email: aghort.info@munters.com / www.munters.com



Additional Elite Plus Features

Safety features:

- High & low static pressure alarm
- High and low temp alarm
- Water spill alarm
- Feed over run alarm
- Individuale Probe alarms

Track History: (180 days)

- Temperature Hi/Lo
- Heater Run Time
- Relative Humidity Hi/Lo
- Static Pressure Hi/Lo
- Daily and total Water Consumption
- Feeder Run Time
- Animal Mortality - Daily/Total

Start / Stop Temperatures:

- Summer Start/Stop temperatures
- Night time set-points
- Winter Start/Stop temperatures adjustable for each fan, cooling & heating stage
- Minimum Ventilation ramping and compensation
- Curve for Temperature and Minimum Ventilation

Vent Doors & Tunnel Curtains:

- Static Pressure, or timer for Vent Doors, second Inlet and Tunnel Curtain
- 10 Inlet controls, timed or Potentiometer
- Pre-opening of Vent Doors, Attic & Tunnel Curtain

Natural Ventilation:

- Up to 4 Natural outputs
- Can run 4 independent zones

Outputs:

- 16 Stages of Fans for Cooling
- 8 Stages of Heating
- 8 Clock Outputs
- 4 independent 0-10V outputs
- Tunnel Curtain
- Vent Doors
- Alarm Contacts

Inputs:

- 8 Temperature Sensors
- 1 Outside Temperature Sensor
- Relative Humidity
- 2 Water Meter
- Static Pressure built-in
- Computer Compatible with Interface
- 2 Feeder inputs

Elite Plus Relay Panel Features

- Pre-wired Relay Panel
- Three way ON/OFF/AUTO switches on relay panel
- Up to 96 heavy duty relays



Accessories

- Agri-Alert Alarm System
- Humidity sensors
- Backup relay box
- Water meters
- Inlet Controls - SB3xxx
- Light Dimmer
- DI-8, adds up to 16+ water meters

Agri-Alert System

Agri Alarm systems are designed to detect common site problems and failures, and to Quickly and reliably communicate them to those who need to know .

AgriAlert 800 EZ



Agri Alert 128 Touch



TP-8 Transponder



Wireless RS485



TR-2 Transponder



KP-8 Keypad



Australia Munters Pty Limited, Phone +61 2 8843 1594, **Brazil** Munters Brasil Industria e Comercio Ltda, Phone +55 41 3317 5050, **Canada** Munters Corporation LANSING, Phone +1 517 676 7070, **China** Munters Air Treatment Equipment (Beijing) Co. Ltd, Phone +86 10 80 418 000, **Denmark** Munters A/S, Phone +45 9862 3311, **India** Munters India, Phone +91 20 3052 2520, **Indonesia** Munters, Phone +62 818 739 235, **Italy** Munters Italy S.p.A., Chiusavecchia, Phone +39 0183 52 11, **Japan** Munters K.K., Phone +81 3 5970 0021, **Korea** Munters Korea Co. Ltd., Phone +82 2 761 8701, **Mexico** Munters Mexico, Phone +52 818 262 54 00, **Russia** Munters AB, Phone +7 812 448 5740, **Singapore** Munters Pte Ltd., Phone +65 744 6828, **South Africa and Sub-Sahara Countries** Munters (Pty) Ltd., Phone +27 11 997 2000, **Spain** Munters Spain S.A., Phone +34 91 640 09 02, **Sweden** Munters AB, Phone +46 8 626 63 00, **Thailand** Munters Co. Ltd., Phone +66 2 642 2670, **Turkey** Munters Form Endüstri Sistemleri A.Ş, Phone +90 262 751 3750, **USA** Munters Corporation Lansing,MI Phone +1 517 676 7070, **Vietnam** Munters Vietnam, Phone +84 8 3825 6838, **Export & Other countries** Munters Italy S.p.A., Chiusavecchia Phone +39 0183 52 11.