


CT Cooling (continue on next page)



CT Cooling (continued)

Item	Catalog No.	Description	Qty.
1	JP3018	8" Dia. Air Pipe (PIP 50) White PVC	varies/foot
2	EC1328	Pipe Support Bracket, without holes	varies/foot
3	EC1330	Pipe Support Bracket, with holes	varies/foot
4	KS2105	Lag Screw, #14 x 1½", Stainless Steel	varies
5	KS2462	Lag Screw, ⅜" x 3½", Zinc Plated	varies
6	KS2257	TEK Screw, #10 x 1¼" Hex Washer, Stainless Steel	varies
7	EC1340	Drip Collector Splice, 6"W., plastic	varies
8	EC1290	Drip Collector, 2'L., White PVC	varies
	EC1291	Drip Collector, 4'L., White PVC	varies
	EC1296	Drip Collector, 5'L., White PVC	varies
	EC1294	Drip Collector, 10'L., White PVC	varies
9	EC1148	Drain Fitting, 1" x ¾", Schedule 40	varies
10*	CEL1545061272MI	Pad Material (see Price Catalog - Cooling section)	varies
11	EC1046	End Panel, 75.25"H., Plastic	2
12	EC1310	Drip Collector End Cap	2
13	EC1299	Pipe Nipple 1½" x 10"L. Schedule SDR21 PVC	2
14	EC1224	Ball Valve, 1½" Slip, Schedule 40 PVC	1
15	EC1298	Distribution Pipe, 1½" Dia. with ⅛" Dia. holes, 3" O.C.	varies
16	KN2302	Wing Nut, ⅝" Dia., Nylon	varies
17	KS1009	Bolt, 6" x ⅝" Dia., Stainless Steel	varies
18	EC1031	Pipe Holder for 1½" Dia., Aluminum	varies
19	EC1226	Slip Cap, 1½" Schedule 40 White PVC	1
20	KS2252	TEK Screw, #10 x ¾", Stainless Steel	1
21	EC1078	Distribution Cap, 2' L., Aluminum	varies/foot
	EC1072	Distribution Cap, 4' L., Aluminum	varies/foot
	EC1079	Distribution Cap, 5' L., Aluminum	varies/foot
	EC1076	Distribution Cap, 10' L., Aluminum	varies/foot
22	EC1202	Angle Bracket, 1½" x 4" x 1½", Stainless Steel	2
23	Standard Pad Retainer		
	EC1071	Pad Retainer, 2' L., Aluminum	varies/foot
	EC1065	Pad Retainer, 4' L., Aluminum	varies/foot
	EC1070	Pad Retainer, 5' L., Aluminum	varies/foot
	EC1068	Pad Retainer, 10' L., Aluminum	varies/foot
	Optional: Open Header Pad Retainer		
	EC1902	Pad Retainer, Open Style, 2' L., Aluminum	varies/foot
	EC1904	Pad Retainer, Open Style, 4' L., Aluminum	varies/foot
	EC1905	Pad Retainer, Open Style, 5' L., Aluminum	varies/foot
	EC1910	Pad Retainer, Open Style, 10' L., Aluminum	varies/foot