



Item	Catalog No.	Description	Qty.
1	FH3414	Housing, 14" VX Fan with Clips & Labels, FG	1
	FH3416	Housing, 16" VX Fan with Clips & Labels, FG	1
	FH3418	Housing, 18" VX Fan with Clips & Labels, FG	1
	FH3424	Housing, 24" VX Fan with Clips & Labels, FG	1
	FH3127	Housing, 26" VX Fan with Clips & Labels, FG	1
2	FH1968	Pivoting Shutter Clip, PL	3
3	FP1031SS	Propeller, 14"DD, 6-Blade, Set Screws, AL	1
	FP1038SS	Propeller, 16"DD, 7-Blade, Set Screws, AL	1
	FP1008SS	Propeller, 18"DD, 5-Blade, Set Screws, AL	1
	FP1033SS	Propeller, 24"DD, 4-Blade, Set Screws, AL	1
	FP1126SS	Propeller, 26"DD, 3-Blade, Set Screws, AL	1
4	FH1008	14" Fan, Motor Mount, PVC Coated	1
	FH1009	16"/18" Fan, Motor Mount, PVC Coated	1
	FH1010	24" Fan, Motor Mount, PVC Coated	1
	FH2526	26" Fan, Motor Mount, PVC Coated	1
5	FM1010	14" DD, Motor, 1/8 HP, 1625 RPM, 48 Fr., 1 ph., 115/230V	1
	FM1043	16" DD, Motor, 1/4 HP, 1625 RPM, 48 Fr., 1 ph., 115/230V	1
	FM1009	18" DD, Motor, 1/3 HP, 1625 RPM, 48 Fr., 1 ph., 115/230V	1
	FM1008	24"/26" DD, Motor, 1/3 HP, 1075 RPM, 48 Fr., 1 ph., 115/230V	1
	FM1074	24"/26" DD, Motor, 1/3 HP, 1140 RPM, 48 Fr., 3 ph., 230/460V	1
6	PT0914	Shutter for 14" Fan, 16 3/4" SQ., Belled Inlet, White Plastic	1
	PT1618	Shutter for 16"/18" Fan, 21 5/8" SQ., Belled Inlet, White Plastic	1
	PT24	Shutter for 24" Fan, 27 5/8" SQ., Belled Inlet, White Plastic	1
	PT26	Shutter for 26" Fan, 29.4" SQ., Belled Inlet, White Plastic	1
7	PZ0914	Shutter for 14" Fan, 16 3/4" SQ., White Plastic	1
	PZ1618	Shutter for 16"/18" Fan, 21 5/8" SQ., White Plastic	1
	PZ24	Shutter for 24" Fan, 27 5/8" SQ., White Plastic	1
	PV26	Shutter for 26" Fan, 29.4" SQ., White Plastic	1