

# WS55

## SWINE FINISHER FAN

### FEATURES


- Powerful and highly efficient motor will provide 30,000 cfm and 18.3 cfm/watt at 0.10" static pressure giving you the best efficiency and airflow
- Premium fiberglass housing, stainless steel and powder coated components to ensure long life in the tough swine environment
- Fiberglass housing is UV resistant and durable
- HDPE UV Stabilized Cone
- Proven drive assembly using an automotive grade bearing with exceptional durability requires no maintenance
- Simple mono-strut construction
- 55" for peak performance
- Custom motor designed to optimize air flow and efficiency
- Uses internal PVC shutter



© WS55 Copyright Munters Corporation 2020

## WS55 – NEW LINE OF SWINE FINISHER FANS

Munters, the leader in agricultural ventilation systems debuts the newest addition to the line of fiberglass exhaust fans, the WS55 Shutter Fan. Building on the successful WM54 Wall Mount Damper Fan Series, the WS55 includes a shutter, while still targeting the needs of the swine market. The new WS55 fan uses Munters premium fiberglass construction and many of the same components from the WM54 Fan Series to create a durable, corrosion resistant product at an economical price point. The WS Series is manufactured in Michigan along with most of Munters agriculture products. With over 70 years of fan design and manufacturing experience, Munters has the quality you can trust.



Munters Corporation, Business Area FoodTech


2691 Ena Drive, Lansing, MI 48917 USA / Phone: +1 800-227-2376 Fax: 517-676-7078

Email: [aghort.info@munters.com](mailto:aghort.info@munters.com) / [www.munters.com](http://www.munters.com)



## Dimensions

A	63 <sup>5</sup> / <sub>8</sub> "
B	62 <sup>3</sup> / <sub>4</sub> "
C	64 <sup>7</sup> / <sub>16</sub> "
D	66 <sup>1</sup> / <sub>4</sub> "
E	25 <sup>5</sup> / <sub>16</sub> "
F	11 <sup>3</sup> / <sub>4</sub> "
G (Above W.O.)	<sup>5</sup> / <sub>8</sub> "
H (Below W.O.)	4 <sup>3</sup> / <sub>8</sub> "
Wall Openings (W.O.)	60"W x 61 <sup>1</sup> / <sub>4</sub> "H



## Performance Information:

Catalog Number	0.0"SP		0.05" SP		0.10" SP		0.15" SP		BESS Lab Test #
	CFM	CFM Watt	CFM	CFM Watt	CFM	CFM Watt	CFM	CFM Watt	
Single Phase Motor : 1.5 HP, 115V/208-230V									
WS5515P1CT-PE	32,500	22.1	31,100	20.1	29,900	18.3	28,400	16.6	19438




## COMPLETE YOUR FINISHER VENTILATION SYSTEM WITH MUNTERS PRODUCTS



**BI28**  
Airflow is maximized over the entire static pressure range and flow direction is precisely controlled. Performance of your ventilation system is maximized with air delivered to every part of the building.



**CT Evaporative Cooling System**  
Munters offers a premium, integrated evaporative cooling system designed with corrosion resistant extruded aluminum header, deflector ensuring uniform pad wetting and removable pad retainer.



**LA Actuator**  
Dependable self-locking worm gear units with completely integrated limit switches. The drives will perform for decades without requiring maintenance. Available in 900 lb & 2000 lb versions.



**VX Series Fans**  
VX 18 VX 24 VX 36  
Munters premium exhaust fan line. Withstands corrosive gases from the internal environment and weather exposure from the external environment.



**BA4000**  
4,000 lb. capacity reduces the number of machines needed for longer buildings. Unique ball bearing screw design provides lower power use and increased reliability.



**Australia** Munters Pty Limited, Phone +61 2 8843 1594, **Brazil** Munters Brasil Industria e Comercio Ltda, Phone +55 41 3317 5050, **Canada** Munters Corporation Lansing, Phone +1 517 676 7070, **China** Munters Air Treatment Equipment (Beijing) Co. Ltd, Phone +86 10 80 418 000, **Denmark** Munters A/S, Phone +45 9862 3311, **India** Munters India, Phone +91 20 3052 2520, **Indonesia** Munters, Phone +62 818 739 235, **Italy** Munters Italy S.p.A., Chiusavecchia, Phone +39 0183 52 11, **Japan** Munters K.K., Phone +81 3 5970 0021, **Korea** Munters Korea Co. Ltd., Phone +82 2 761 8701, **Mexico** Munters Mexico, Phone +52 818 262 54 00, **Russia** Munters AB, Phone +7 812 448 5740, **Singapore** Munters Pte Ltd., Phone +65 744 6828, **South Africa and Sub-Sahara Countries** Munters (Pty) Ltd., Phone +27 11 997 2000, **Spain** Munters Spain S.A., Phone +34 91 640 09 02, **Sweden** Munters AB, Phone +46 8 626 63 00, **Thailand** Munters Co. Ltd., Phone +66 2 642 2670, **Turkey** Munters Form Endüstri Sistemleri A.Ş, Phone +90 262 751 3750, **USA** Munters Corporation Lansing, Phone +1 517 676 7070, **Vietnam** Munters Vietnam, Phone +84 8 3825 6838, **Export & Other countries** Munters Italy S.p.A., Chiusavecchia Phone +39 0183 52 11.

Your closest distributor