

Product sheet

Munters MLT800

Desiccant dehumidifier
with AirC



Features

- Advanced control panel
 - diagnostic fault display
- High airflow capacity
- Minimal energy consumption
- Unique plastic rotor casing is 100% corrosion-resistant
- Efficiently dehumidifies down to -20°C.
- Easy-to-install interchangeable front and back panels

Taking dehumidifiers into the future

For over half a century, Munters has been the leading pioneer within humidity control, and we're just getting started.

The MLT800 desiccant dehumidifier with Munters AirC is designed to efficiently dehumidify high airflow applications using minimal energy. It features an internally sealed rotor unit with a durable thermoset plastic casing. The casing has isolated sections for precise balance in dehumidification, reactivation, and heat recovery airflows. The rugged metal frame and access panels are made from corrosion-resistant Aluzink®

Munters AirC is a future-proof control system designed by Munters and provides flexibility and functionality like no other. It ensures your dehumidifier operates at its most energy efficient, and features advanced sensing, multiple communication support and alarm handling.

This technology represents 60 years of innovation and application knowledge for perfect control of the dehumidification process.


Munters MLT800

Desiccant dehumidifier with AirC

Dimensions

A: Width	715 mm
B: Depth	590 mm
C: Height	1310 mm
D: Diameter	160 mm
E: Diameter	100 mm
Weight	125 kg

Measurement diagram for reference only.




Technical specifications

Process air		
Rated airflow	(m ³ /h)	800
Available static pressure	(pa)	200
Reactivation air		
Rated airflow	(m ³ /h)	155
Available static pressure	(pa)	200
Miscellaneous data		
Operating temperature	(°C)	-20/+40
Sound power level to room Lw(A) dB, all inlets and outlets ducted	-	67
Air filter standard	-	G3
IEC protective class (unit)	-	IP33
IEC protective class (electrical)	-	IP54

Total power voltage & current (amps & phase)		
Total power, electrical	(kW)	5.12
220V 3-50Hz	(A)	14.9
220V 3-60Hz	(A)	15.4
230V 3-50Hz	(A)	14.9
230V 3-60Hz	(A)	15.0
380V 3-50Hz	(A)	8.6
380V 3-60Hz	(A)	8.9
400V 3-50Hz	(A)	8.5
415V 3-50Hz	(A)	8.4
440V 3-60Hz	(A)	7.8
460V 3-60Hz	(A)	7.6
480V 3-60Hz	(A)	7.5
500V 3-50Hz	(A)	6.9

Options

- Hours run counter (monitors the number of hours the system is operational)
- Blocked filter alarm
- Rotor stopped alarm
- Humidity control system with alarm and display (refer to the RH98 product data sheet)
- Air cooled condenser (refer to the MLT800L product data sheet)
- Stainless steel sheet metal casing



Find your nearest Munters office at www.munters.com

Munters reserves the right to make alterations to specifications, quantities, etc., for production or other reasons, subsequent to publication. © Munters AB, 2023