



Want to control your indoor climate and save energy?

The Munters ComDry portable dehumidifier range has been controlling climates in remote spaces for many years, with over 25.000 units produced. Owners around the world have come to trust this quality portable dehumidifier. But they've been asking for more. A dehumidifier that's even more reliable, with improved drying capacity and, most importantly, low energy consumption.

Munters has listened and can now proudly introduce the all-new Munters ComDry NX - an extremely reliable and portable dehumidifier with superior drying capacity that is not only lightweight and easy to install but also 20% more energy-efficient than most competitors. The best has become even better.

Featuring convenient plug-and-play, cutting-edge control system, new drive motor and a wireless display for remote control, this best-in-class portable plug-and-play dehumidifier creates the perfect climate for indoor environments such as windmills,

storage facilities, museums and waterworks. And the new design with an elegant, black casing lets you place your ComDry NX in any environment.

Its intelligent control system adapts heat and output based upon room conditions, controlling the climate as precisely and efficiently as possible.

Munters knows how important it is to create the perfect climate while at the same time saving energy is to our customers. Upgrading to a ComDry NX will not only help the environment, but it will also enhance your bottom line.



**New Munters ComDry NX series
– the best just got better**

ComDry NX

Quick facts



ComDry NX M190Y

- Measurements: 445 x 270 x 381 mm (WxDxH)
- Weight: 11.5 kg
- Maximum airflow: 225 m³/h
- Total power: 0.95 kW
- Max noise level: 58 dB(A)



ComDry NX M210X

- Measurements: 445 x 270 x 571 mm (WxDxH)
- Weight: 15 kg
- Maximum airflow: 240 m³/h
- Total power: 1.01 kW
- Max noise level: 58 dB(A)



ComDry NX M160L

- Measurements: 445 x 270 x 571 mm (WxDxH)
- Weight: 17 kg
- Maximum airflow: 160 m³/h
- Total power: 1.01 kW
- Max noise level: 58 dB(A)



ComDry NX M170L

- Measurements: 445 x 270 x 571 mm (WxDxH)
- Weight: 17 kg
- Maximum airflow: 170 m³/h
- Total power: 1.02 kW
- Max noise level: 58 dB(A)