

Product sheet  
CC247 Elite Control

- Large 16 line LCD screen with Elite model
- Up to 100 heavy duty relays
- Programmable Configuration Chip
- Unmatched lightning protection
- Track history 60 to 75 days
- Available message center
- 2 Box system
- Remote communications package available
- User defined hot keys
- Water spill alarm
- Current building conditions shown on screen
- Installer password can be set for protection
- Curve for Temperature and Minimum Ventilation

CC247 Elite© Copyright Munters Corporation

## CC247 Elite Control

The Elite offers around the clock performance with the CC24-7 series. The CC24-7 Series is designed with a user friendly interface, expand ability and many other features which make it the ultimate building management tool. The Elite offers a number of added benefits, including a large 16 line LCD screen, message center, programmable hot keys and much more.

This control is compatible with a variety of accessories that will further enhance your building management. Humidity sensors, static pressure module, backup relay box, water meters, Site Watch production management software and Agri-Alert alarm system are a few of the accessories.



Munters Corporation, Business Area AgHort

4215 Legion Drive Mason, MI 48854-1036 USA / Phone: +1 517-676-7070 Fax: 517-676-7078  
Email: aghort.info@munters.com / www.munters.us



## Additional Elite Features

### Safety features:

- High & low static pressure alarm can operate Tunnel Curtains, Vent Doors and Fans

### Track History:

- Temperature Hi/Lo
- Heater Run Time
- Relative Humidity Hi/Lo
- Static Pressure Hi/Lo
- Daily Water Consumption

### Start / Stop Temperatures:

- Summer Start/Stop temperatures
- Winter Start/Stop temperatures
- Fully adjustable for each fan, cooling & heating stage

### Vent Doors & Tunnel Curtains:

- Static Pressure, Potentiometer or Timer for Vent Doors
- Timer for Inlets built-in
- Pre-opening of Vent Doors & Tunnel Curtain Adjustable parameters for temperature fluctuations

### Natural Ventilation:

- Up to 4 natural outputs
- Can run 4 independent zones
- Day curve for 4 of the 8 clocks to allow for ramping programs
- 4 separate programs for Stages 1-6

### Outputs:

- 16 Stages of Fans & Cooling
- 8 Stages of Heating
- 8 Clock Outputs
- Tunnel Curtain
- Vent Doors
- Alarm Contacts

### Inputs:

- 8 Temperature Sensors
- 1 Outside Temperature Sensor
- Relative Humidity
- Pulsed Water Meter
- Static Pressure built-in
- Computer Compatible with Interface

## Elite Relay Panel Features

- Pre-wired Relay Panel
- Three way ON/OFF/AUTO switches on relay panel
- Large LCD 16 display lines
- Up to 100 heavy duty relays
- Dusk til dawn lighting program
- Tunnel Curtain on timer or Static Pressure
- Mortality Feature
- User defined hot keys
- Message center
- Track history
- Water spill alarm
- Up to four 0-10V outputs
- Night time set-points
- Led indicators for easy viewing of current conditions
- Multiple pulsed water meter inputs
- Independent cooling stages for pad or misting systems
- Minimum ventilation ramping and compensation


## Accessories

- Humidity sensors
- Backup relay box
- Water meters
- VSM-2 Variable Speed Module
- Agri-Alert Alarm System
- Site Watch
- Production Management Software




Agri-Alert Alarm System has outdoor temperature compensation, maximum surge protection, ability to track alarm history and status reports on each zone.

## Site Watch Production Management Software



Track environmental conditions, water, feed, animal weights and much more in real time, 24/7.



Increase your efficiency and profitability by providing you with a complete set of conditions in real time 24/7. Works with all Munters CC247 Series controls.



**Australia** Munters Pty Limited, Phone +61 2 8843 1594, **Brazil** Munters Brasil Industria e Comercio Ltda, Phone +55 41 3317 5050, **Canada** Munters Corporation Mason, Phone +1 517 676 7070, **China** Munters Air Treatment Equipment (Beijing) Co. Ltd, Phone +86 10 80 418 000, **Denmark** Munters A/S, Phone +45 9862 3311, **India** Munters India, Phone +91 20 3052 2520, **Indonesia** Munters, Phone +62 818 739 235, **Italy** Munters Italy S.p.A., Chiusavecchia, Phone +39 0183 52 11, **Japan** Munters K.K., Phone +81 3 5970 0021, **Korea** Munters Korea Co. Ltd., Phone +82 2 761 8701, **Mexico** Munters Mexico, Phone +52 818 262 54 00, **Russia** Munters AB, Phone +7 812 448 5740, **Singapore** Munters Pte Ltd., Phone +65 744 6828, **South Africa and Sub-Sahara Countries** Munters (Pty) Ltd., Phone +27 11 997 2000, **Spain** Munters Spain S.A., Phone +34 91 640 09 02, **Sweden** Munters AB, Phone +46 8 626 63 00, **Thailand** Munters Co. Ltd., Phone +66 2 642 2670, **Turkey** Munters Form Endüstri Sistemleri A.Ş, Phone +90 262 751 3750, **USA** Munters Corporation Mason, Phone +1 517 676 7070, **Vietnam** Munters Vietnam, Phone +84 8 3825 6838, **Export & Other countries** Munters Italy S.p.A., Chiusavecchia Phone +39 0183 52 11.