



400V 15kW

T - Thermostat
 B - Switch
 M - Motor
 TV - Safety thermostat
 D - Heating element (230V 2500W)
 T1 - Time-delay thermostat

SWITCH

- OFF
- ⊗ POS.1
- ⌒ POS.1+2/5
- ⌒⌒ POS.1+2/5+3/7
- ⌒⌒⌒ POS.1+2/5+3/7+6/8

	1	2	3	4	5	6	7	8	
	P1	P2	P3	P4	P5	P6	P7	P8	
0									0°
1	⊗								72°
2	⊗	⊗							144°
3	⊗	⊗	⊗						216°
4	⊗	⊗	⊗	⊗					288°

400V 3 50Hz

00	04/12/09	First issue					D. Fulcheri
Rev.No	Date	Description					Drawer
Linear dimension range	up to 6	over 6 up to 30	over 30 up to 120	over 120 up to 400	over 400 up to 1000	over 1000 up to 2000	over 2000 up to 4000
tolerance limits	±0.3	±0.5	±0.8	±1.2	±2	±3	±4

Description Schema elettrico RPL 15 FT (made in China) RPL 15 FT wiring diagram (made in China)			Drawing No SCH091	
Material -			Thickness -mm	Drawer D. Fulcheri
 MUNTERS ITALY S.p.A. - Mondovi This drawing is exclusive property of MUNTERS ITALY S.p.A.. Any vision, reproduction or release without written authorization by MUNTERS ITALY S.p.A. is ABSOLUTELY FORBIDDEN			Weight -kg	Latest revision approved by <i>P. A. Oda</i>
			Drawing scale -	Date 04/12/2009
			DIMENSIONS WITHOUT TOLERANCE LIMITS: ROUGH PRECISION LEVEL UNI EN 22768-1/2	
			Purchased part No -	
			Manufactured part No -	