

ML-L Series with Air Cooled Condenser



Product Description

The ML270L desiccant dehumidifier with air cooled condenser is designed to efficiently dehumidify in unheated closed spaces. The wet air from the dehumidifier is passed through the air cooled condenser and then returned to the rotor in a closed loop circuit. The components within the closed loop are constructed of stainless steel and thermoset plastic. Water removed by the condenser is drained away. The heat from the air cooled condenser is then either used in the application or ducted away. Its rugged formed metal frame and access panels are produced from corrosion resistant Aluzink®. The electrical system conforms to established ML-L Series standards as well as to both harmonised European Standards and to CE marking specifications.

Munters Rotor Technology

The desiccant rotor is manufactured from a corrugated composite material that is highly effective at attracting and holding water vapour. Every Munters dehumidifier applies a unique rotor technology. Airflows, air conditions, rotor sections, and rotor rotation speeds are optimised for specific applications. An innovative control system maximises the units energy efficiency. A characteristic of the ML-L Series rotor technology is an extra rotor sector which provides high capacity, while simultaneously recovering heat, thereby effectively reducing the electrical power requirement. The reactivation air is continually re-circulated.

PRODUCT INFORMATION

ML270L

Features


- Heat recovery – condenser heat available.
- Easy to install – no wet air duct needed.
- Dehumidifies efficient down to -0°C.
- Unique plastic rotor casing 100% corrosion resistance.



Model ML270L

Diagram measurements are for reference only.

Scaled and dimensioned AutoCad drawings are available in Munters DryCap program.



Width (A)	Depth (B)	Height (C)	Diam. (D)	Diam. (E)	Weight
1141 mm	410 mm	1010 mm	160 mm	200 mm	118 kg

Technical Specification

Process Air

Rated airflow (m³/h)	270
Available static pressure (Pa)	200

Reactivation air

Rated airflow (m³/h)	99
----------------------	----

Condenser air

Rated airflow (m³/h)	650
Available static pressure (Pa)	200
Fan motor power (kW)	0,4
Sensible heat, condenser air (kW)	2,0

Total power, voltage and current (amps/phase)

Total power(kW)	3,70
220V 3-50Hz (A)	11,1
230V 3-50Hz (A)	10,3
380V 3-50Hz (A)	6,4
400V 3-50Hz (A)	6,1
415V 3-50Hz (A)	5,9


Miscellaneous Data

Operating temperature (°C)	+0/+25
Max noise level unducted (dBA)	79
Air filter standard	G3
IEC protective class (unit)	IP33
IEC protective class (electrical panel)	IP54

Dehumidification Capacity

Approximate capacity in kg/h at different inlet process air relative humidity, % RH.

Dehumidification capacity, kg/h



Options

- Hours run counter (monitors the number of hours the system is operational)
- Humidity control system with alarm and display
Refer to the RH98 product data sheet
- Stainless steel sheet metal casing

AUSTRALIA

Tel +61 2 8843 1588

CHINA

Tel +86 10 804 18000

INDIA

Tel +91 20 668 18 900

NETHERLANDS

Tel +31 172 43 32 31

SWEDEN

Tel +46 8-626 6300

UNITED KINGDOM

Tel +44 1480 432 243

AUSTRIA

Tel +43 1 6164298-0

DENMARK

Tel +45 4495 3355

ITALY

Tel +39 0183 521377

POLAND

Tel +48 58 305 35 17

SWITZERLAND

Tel +41 52 3438886

UNITED STATES

Tel +1 978 241 1100

BELGIUM

Tel +32 2 240 68 68

FINLAND

Tel +358 20 776 8230

JAPAN

Tel +81 3 5970 0021

SINGAPORE

Tel +65 6744 6828

THAILAND

Tel +66 2 642 2670-3

VIETNAM

Tel +84 8 825 6838

BRAZIL

Tel +55 41 3317 5050

FRANCE

Tel +33 1 3411 5757

KOREA

Tel +82 2 761 8701

SOUTH AFRICA

Tel +27 11 997 2000

TURKEY

Tel +90 262 751 3750

CANADA

Tel +1 905 8585894

GERMANY

Tel +49 40-879690-0

MEXICO

Tel +1 52 722 270-4029

SPAIN

Tel +34 91 640 09 02

UNIT. ARAB EMIRATES

Tel +971 4 8809295

www.munters.com

