



Munters GA 30/95T

Air heaters

Munters GA air heaters are designed to provide cost-effective heating solutions in a wide variety of applications, such as livestock farming (broiler, layer, swine) and greenhouse.

Features

- 100% thermal efficiency
- Run on LPG, butane or propane
- Easy to install and operate
- Double solenoid valve to shut off faulty gas supply
- Safety switch to prevent overheating
- Pressure sensor to detect airflow obstructions
- Stainless steel



GA 30/95T front view

Munters GA 30/95T function according to the principle of direct-fired heating. As the air passes through the combustion chamber where the burner is located, 100% of the fuel is converted and transferred to the airflow. The maximum thermal efficiency reduces energy consumption and operating costs.

To ensure a longer service life, even in humid environments, Munters GA air heaters feature the housing and combustion chamber in stainless steel with all electrical components housed in an IP54 enclosure. For safety reasons, Munters GA 30/95T are equipped with a double solenoid valve to close and open the gas supply and a pressure sensor that interrupts it in case of an obstruction of the airflow.

Munters GA models come fully assembled with an electric cord and gas connection pipe with a pressure regulator, ready for use. A mechanical or electronic thermostat is available upon request.

As market leader in ventilation solutions for more than 60 years, Munters guarantees quality and is ISO 9001 certified.




Proudly manufactured with 100% renewable energy in our plants in Italy

Munters GA 30/95T

Air heaters

Dimensions



	A	B	C	D
GA30	645 mm	532 mm	440 mm	370 mm
GA95T	1140 mm	473 mm	608 mm	378 mm

Technical specifications

		GA30	GA95T
Heating power	kW	25 - 36	97
Airflow	m ³ /h [cfm]	1700 [1000]	6000 [3560]
Nominal power	W	110	700
Rated voltage	V		230
Rated frequency	Hz	50	50/60
Rated current	A		4.5
Gas connection			3/8"
Gas consumption	kg/h	1.75 - 2.51	6.9
Gas pressure	bar	0.7	2.0
Weight of fully equipped heater	kg	15	32
Motor protective class			IP54

Load capacity

	GA30	GA95T
20' Container	66	38
40' Container	138	80
40' HC Container	138	120
Truck	204	156

Find your nearest Munters office at www.munters.com

Munters reserves the right to make alterations to specifications, quantities, etc., for production or other reasons, subsequent to publication. © Munters AB, 2021