

Product sheet

Munters MLT800

Desiccant dehumidifier with AirC 800



Features

- Modern AirC 800 control system
- Small footprint requires minimal floor area
- High airflow capacity
- Minimal energy consumption
- Unique plastic rotor casing is 100% corrosion resistant
- Dehumidifies efficient down to -20°C
- Communication and external control options
- Remote monitoring and control

The MLT800 desiccant dehumidifier with AirC 800 control is designed to efficiently dehumidify in low moisture applications.

It is equipped with an internally sealed rotor unit. The rotor casing is constructed of durable thermoset plastic and contains isolated sections that provide a precise balance for dehumidification, reactivation, and heat recovery airflows. Its rugged formed metal frame and access panels are produced from corrosion resistant materials.

The modern control system is equipped with a number of alarm functions to ensure total control of the dehumidification process.

The MLT800 dehumidifiers conforms to UL and CE marking specifications, RoHS and to the below standards:

- EU 60204-1:2018
- EU 61000-6:2019
- EN IEC 61000-6-3:2021
- UL 60335-2-40
- CSA C22.2#60335-2-40

Munters MLT800


Desiccant dehumidifier with AirC 800

Dimensions, mm/kg [inch/lb]

| | | |
|-------------|------|--------|
| A: Width | 720 | [29] |
| B: Depth | 600 | [24] |
| C: Height | 1310 | [51.5] |
| D: Diameter | 160 | [6.3] |
| E: Diameter | 100 | [3.9] |
| Weight | 141 | [311] |

- 1. Process air in
- 2. Dry air out
- 3. Reactivation air
- 4. Wet air

Measurement diagram for reference only.



Technical specifications


| Process air | | |
|---|-----------|------------|
| Rated airflow | 800 m³/h | 471 CFM |
| Available static pressure | 200 pa | 200 pa |
| Reactivation air | | |
| Rated airflow | 155 m³/h | 91 CFM |
| Available static pressure | 200 pa | 200 pa |
| Miscellaneous data | | |
| Operating temperature | -20/+40°C | -13/+104°F |
| Sound power level to room Lw(A) dB, all inlets and outlets ducted | 67 dBA | 67 dBA |
| Air filter standard | G3 | G3 |
| IEC protective class (unit) | IP33 | IP33 |
| IEC protective class (electrical) | IP54 | IP54 |

| Total power voltage & current (amps & phase) | | |
|--|---------|---------|
| Total power, electrical | 5.12 kW | 5.12 kW |
| 380V 3-50Hz | 8.6 A | 8.6 A |
| 380V 3-60Hz | 8.9 A | 8.9 A |
| 400V 3-50Hz | 8.5 A | 8.5 A |
| 415V 3-50Hz | 8.4 A | 8.4 A |
| 440V 3-60Hz | 7.8 A | 7.8 A |
| 460V 3-60Hz | 7.6 A | 7.6 A |
| 480V 3-60Hz | 7.5 A | 7.5 A |

Options

- Communication via Modbus, BACnet
- Dewpoint sensor
- External controls
- External filter box M5 or F7
- Insulated process air inlet
- Mirror handed
- Stainless steel casing
- AirC Wireless
- AirC Connect

Dehumidification capacity



Find your nearest Munters office at www.munters.com

Munters reserves the right to make alterations to specifications, quantities, etc., for production or other reasons, subsequent to publication. © Munters AB, 2025