



MC150 Series Desiccant dehumidifier

Features

- Compact design
- Analogue version = plug & play
- Digital version = multiple control options
- High efficiency
- Ducted air in/outlets
- Easy filter change without tools
- Continuous fan mode
- Low noise level
- Various accessories
- Corrosion Class 4
- Digital version has built in RHT sensor with advanced control modes

MC150 Series

The MC series represents a range of desiccant dehumidifiers with high drying capacity, reliability and flexibility. The solid powder coated Aluzinc casing not only withstands corrosion (class 4) but also makes it versatile for a wide range of applications.

The analogue version allows for easy installation and can be equipped with an external humidistat for moisture control and energy saving, mostly for simple storage and preservation applications.

For more sophisticated process applications in food, pharma or other industries, the digital version has control options and functions available.

The Munters rotor technology stands for more than 60 years of customer oriented global experience and reliability.




* Available in analogue or digital version

MC150 Series Technical Specifications


Y = 3 hole dehumidifier; X = 4-hole dehumidifier; A = Analogue; D = Digital

MC150 Models		MC150YA MC150YD	MC150XA MC150XD
Process air			
Maximum airflow	m ³ /h	235	260
Airflow nominal	m ³ /h	150	150
Available static pressure	Pa	150	200
Duct inlet/outlet	mm	100/100	100/100
Reactivation air			
Airflow nominal	m ³ /h	50	50
Available static pressure	Pa	100	150
Duct inlet/outlet	mm	80	80/80
Total power, voltage and current			
Total power	kW	1.08	1.36
Moisture removal, at 20°C/60%	kg/h	0.51	0.70
Operating temperature	°C	-20 - +40	-20 - +40
Voltage	V/Hz	230/50-60	230/50-60
Current	A	4,7	5,9
Noise level	db(A)	57	58
Miscellaneous Data			
IEC protective class (unit)		33	33
IEC protective class (electrical panel)		54	54
Filter class		G3	G3
Dimension			
LxWxH	mm	531x300x384	531x300x507
Weight	kg	18,4 18,7	25,2 25,6

MC150XA/XD



MC150YA/YD



Accessories:

- Wall Bracket

Article No:
170-027708-001

Analogue machines (A):


- MC - Humidistat RH15 170-028562-001
- Junction Box 170-027702-001
- Home Vision 170-027703-001

Digital machines (D):


- External RH/T Sensor Kit 170-027706-001
- HMI Extension Kit 170-027705-001
- Signal cable 0.5 m 170-029048-001
- Signal cable 5 m 170-029049-001
- MC- Humidistat RH 15 170-028562-002

Capacities & Performance

MC150YA/YD _____ MC150XA/XD _____



MC150YA/YD _____ MC150XA/XD _____



Digital machines has a built in RHT sensor that can be controlled on RH, g/kg and dew point.

Australia Phone +61 2 8843 1588, dh.info@munters.com.au Austria Phone +43 1 6164298-92-51, luftentfeuchtung@munters.at Belgium Phone +32 1528 5611, info@muntersbelgium.be Brazil Phone +55 41 3317 5050, munters@com.br Canada Phone +1 905 564 6466, dhinfo@munters.com China Phone +86 10 8048 3493, info@munters.com.cn Czech Republic Phone +420 775 569 657, info@munters-odvlhcovani.cz Denmark Phone +45 4495 3355, info@munters.dk Finland Phone +358 20 776 8230, laitemyynit@munters.fi France Phone +33 1 3411 5757, dh@munters.fr Germany Phone +49 4087 96900, mgd@munters.de India Phone +91 20 668 18 900, info@munters.in Italy Phone +39 0183 52 11, marketing@munters.it Japan Phone +81 3 5970 0021, mkk@munters.co.jp Korea +82 2761 8701, munters@munters.co.kr Mexico Phone +52 81 8262 5400, munters@munters.com.mx Netherlands Phone +31 172 433231, vochtbeheersing@munters.nl Poland Phone +48 58305 3517, dh@munters.pl Singapore Phone +65 6744 6828, info@munters.com.sg South Africa Phone +27 11 997 2000, info@munters.co.za Spain Phone +34 91 640 09 02, marketing@munters.es Sweden Phone +46 8 626 63 00, avfukning@munters.se Switzerland Phone +41 52 343 8886, info.dh@munters.ch Thailand Phone +66 2642 2670, info@munters.co.th Turkey Phone +90 262 751 3750, info@muntersform.com UAE +971 4 8809295, middle.east@munters.com United Kingdom Phone +44 1480 432 243, dryair@munters.co.uk USA Phone +1 978 241 1100, dhinfo@munters.com Vietnam Phone +84 8 8256 838, vietnam@muntersasia.com

