



Product Information
TempMan

- User-friendly and "simple" controller
- Control the capacity of the Breeze fan according to the temperature in the stable
- Ensures that air circulation is sufficient on warm days, and that the air speed does not cause problems in the stable on cold days
- Up to 8 Breeze fans can be connected to 1 TempMan (parallel)
- Ensure the welfare of the livestock

TempMan

TempMan is a controller for the Breeze fan which is used for air circulation in stables with natural ventilation.

The controller is used in stables where the Breeze fan is regulated according to the temperature in the stable.

With this controller, the farmer can adjust the large capacity of the Breeze fan in order to ensure that the air circulation is high enough on warm days or the speed of the air flow in stables on cold days does not cause any problems.



TempMan

Munters A/S,

Nordvestvej, 3 - 9600 Aars, Denmark / Phone: +45 986 233 11 / Fax +45 986 213 54 / www.munters.dk/agro

Product description

With the TempMan is possible to set the temperature at which the Breeze fan must start. It is also possible to set how the Breeze fan must react according to the change in temperature and minimum and maximum rotation speed of the fan.

The breeze fan can work as manual operated, but with the TempMan and the automatic control, the effect on the climate in the stable will be even more significant.

- EMC TESTED
- CE APPROVED

Technical data

Power	230 V
Temperature sensor	1
Output	2 pcs 0-10V
Relay output	1 pcs
Max/min output	adjustable
XP-tape	adjustable
Adjustable temp. set point	5-45°C
Density	IP54
Measure	130x80x60 mm



Australia Munters Pty Limited, Phone. +61 2 8843 1594, **Brazil** Munters Brasil Industria e Comercio Ltda, Phone +55 41 3317 5050, **Canada** Munters Corporation Mason, Phone +1 517 676 7070, **China** Munters Air Treatment Equipment (Beijing) Co. Ltd, Phone +86 10 80 418 000, **Denmark** Munters A/S, Phone +45 9862 3311, **India** Munters India, Phone +91 20 3052 2520, **Indonesia** Munters, Phone +62 818 739 235, **Italy** Munters Italy S.p.A., Chiusavecchia, Phone +39 0183 52 11, **Japan** Munters K.K., Phone +81 3 5970 0021, **Korea** Munters Korea Co. Ltd., Phone +82 2 761 8701, **Mexico** Munters Mexico, Phone +52 818 262 54 00, **Singapore** Munters Pte Ltd., Phone +65 744 6828, **South Africa and Sub-Sahara Countries** Munters (Pty) Ltd., Phone +27 11 997 2000, **Spain** Munters Spain S.A., Phone +34 91 640 09 02, **Sweden** Munters AB, Phone +46 8 626 63 00, **Thailand** Munters Co. Ltd., Phone +66 2 642 2670, **Turkey** Munters Form Endüstri Sistemleri A.Ş, Phone +90 262 751 3750, **USA** Munters Corporation Mason, Phone +1 517 676 7070, **Vietnam** Munters Vietnam, Phone +84 8 3825 6838, **Export & other countries** Munters Italy S.p.A., Chiusavecchia Phone +39 0183 52 11

Your closest distributor