



Product information  
MDC: Munters Duplex Curtain


- Curtain protects against wind and severe weather conditions
- Variable opening
- Curtain opens from top down or from bottom up
- Manufactured in UV resistant PVC coated high tenacity polyester
- Anti-static treatment repels dirt (straw, sand, dust)
- "Click & Go" wind pipes enabling vehicular access directly into shed
- Optimal light transmission

## MDC: Munters Duplex Curtain

The Munters Duplex curtain is typically installed in livestock installations, where direct vehicular access from outside into the individual pen is required (for cleaning or other purposes).

The Munters Duplex curtain combines the traditional ventilation function with easy access by vehicle(s) into the shed or barn.

Duplex opens up/down or down/up in accordance with your requirements. The curtain can be supplied with removable wind pipes in cases where a wider access is required (larger vehicles).



MDC: Duplex

Munters A/S,

Nordvestvej, 3 - 9600 Aars, Denmark / Phone +45 986 233 11 / Fax +45 986 213 54 /  
[www.munters.dk/agro](http://www.munters.dk/agro)



## Product description


The Duplex curtain is manufactured in heavy duty, UV resistant PVC coated high tenacity polyester. The light grey color ensures optimal light transmission. The curtain is anti-static and will repel dirt (sand, straw, dust). The curtain rolls on an extruded aluminum profile.

As safety against strong winds, specially designed wind pipes are installed at intervals of 2 meters (recommended distance – distance varies depending on opening height). The wind pipes are made of galvanized iron with an outer plastic pipe – the latter to minimize wear and tear on both wind pipe and curtain. Wind pipes are installed on the outside and inside of the curtain, acting as a guide for the curtain.

In cases where an even wider access into the shed is required (wider than the recommended 2 m distance between the wind pipes), the Duplex curtain can be delivered with detachable wind pipes - the so-called "Click & Go" solution. With "Click & Go", the wind pipes are easily "clicked out" from their normal position between the steel trusses on the building – thus enabling a wider access.

### Technical data

Max height	4 meter
Max length	100 meter (maximum 300 m <sup>2</sup> per section)
Power	3 phase 400V
Function	Roll from the top/down and down/up
Accessories	Removable windpipes



**Australien** Munters Pty Limited, Phone +61 2 8843 1594, **Brasilien** Munters Brasil Industria e Comercio Ltda, Phone +55 41 3317 5050, **Canada** Munters Corporation Mason, Phone +1 517 676 7070, **Kina** Munters Air Treatment Equipment (Beijing) Co. Ltd, Phone +86 10 80 418 000, **Denmark** Munters A/S, Phone +45 9862 3311, **India** Munters India, Phone +91 20 3052 2520, **Indonesien** Munters, Phone +62 818 739 235, **Italien** Munters Italy S.p.A., Chiusavecchia, Phone +39 0183 52 11, **Japan** Munters K.K., Phone +81 3 5970 0021, **Korea** Munters Korea Co. Ltd., Phone +82 2 761 8701, **Mexico** Munters Mexico, Phone +52 818 262 54 00, **Singapore** Munters Pte Ltd., Phone +65 744 6828, **Sydafrika & landene syd for Sahara** Munters (Pty) Ltd., Phone +27 11 997 2000, **Spanien** Munters Spain S.A., Phone +34 91 640 09 02, **Sverige** Munters AB, Phone +46 8 626 63 00, **Thailand** Munters Co. Ltd., Phone +66 2 642 2670, **Tyrkiet** Munters Form Endüstri Sistemleri A.Ş, Phone +90 262 751 3750, **USA** Munters Corporation Mason, Phone +1 517 676 7070, **Vietnam** Munters Vietnam, Phone +84 8 3825 6838, **Export & other countries** Munters Italy S.p.A., Chiusavecchia Phone +39 0183 52 11

Munters reserves the right to make alterations to specifications, quantities, etc., for production or other reasons, subsequent to publication.

© Munters, 2015

Your closest distributor