

## Product sheet

# Munters VU Ventilation unit



### Features

- Particularly smooth running and powerful crossflow blower for optimal and homogeneous distribution of humidified air in the room
- Specially developed steam outlet nozzle for condensate-free steam outlet
- Quick and easy installation of the ready-to-connect unit
- Discreet and modern design for unobtrusive room integration

### Technical specifications

Ventilation unit	VU10	VU30
Max. steam output [kg/h]	10	30
Spreading width at max. steam output [m]	3	5
Sound level (at 1m distance, fan only) [dB(A)]	49	51
Steam inlet	DN40	
Condensate outlet	-	DN12
Operating voltage	220-240V / 1 / N	
Dimensions W x H x D [mm]	270 x 130 x 260	490 x 170 x 330
Weight [kg]	4.3	9.0

Find your nearest Munters office at [www.munters.com](http://www.munters.com)

Munters reserves the right to make alterations to specifications, quantities, etc., for production or other reasons, subsequent to publication. © Munters AB, 2023