

Product Information

MVP - Munters ventilation panels

- Optimal airflow for minimum cold ventilation.
- Avoid draft and protect livestock against wind and weather
- Reduction of temperature loss inside barn/stable during cold winter days.
- Double walled, 10 mm, UV resistant Lexan PC sheet material with 10 years limited warranty on light transmission
- Optimal transparency
- Sections of 3m width and varying opening height up to 1,4 m
- Easy installation (lightweight construction, mounted directly on barn/stable walls, few moving parts)
- Operation options: manual, powered units with thermostat control or manual switch - which ever matches your requirements
- Optional netting/bird guard available


MVP - Munters ventilation panels

By choosing the ideal solution to provide natural ventilation for your barn/stable, you greatly increase the livestock welfare and thereby your production yield. Munters ventilation panels (MVP) provides an excellent combination of ventilation control and light requirements as an integral part of the natural ventilation for livestock stables and milking parlours.



MVP - Munters ventilation panels

Installation of Munters ventilation panels



Insulated and UV resistant Lexan PC (PolyCarbonate) sheets form the basis of the MVP solution, which has been developed to accommodate increased requirements for insulation and light dispersion in the barn/stable. The sheet profile and technical specification provides a rugged and weather proof solution with optimum translucency, performance and ease of operation.

The PC sheets are mounted in frame sections of 3 meters in width and varying heights in accordance with your requirements.

MVP - Munters ventilation panels are developed and produced by Munters A/S, Denmark



Australia Phone +61 2 8843 1594, agh.info@munters.com.au, **Brazil** Phone +55 41 3317 5050, contato@munters.com, **Canada** Phone +1 517 676 7070, aghort.info@munters.com, **China** Phone +86 10 8048 3493, marketing@munters.cn, **Denmark** Phone +45 98 623 311, aghort@munters.dk, **India** Phone +91 20 6681 8900, info@munters.in, **Indonesia** Phone +66 2 642 2670, info@munters.co.th, **Italy** Phone +39 0183 5211, info@munters.it, **Japan** Phone +81 3 5970 0021, mkk@munters.jp, **Korea** Phone +82 2 7618 701, munters@munters.co.kr, **Mexico** Phone +52 818 2625 400, dhinfo@munters.com, **Singapore** Phone +65 7 446 828, info@munters.com.sg, **South Africa and Sub-Sahara Countries** Phone +27 11 997 2000, info@munters.co.za, **Spain** Phone +39 0183 5211, info@munters.it, **Sweden** Phone +46 8 6266 300, info@munters.se, **Thailand** Phone +66 2 6422 670, info@munters.co.th, **Turkey** Phone +90 262 7513 750, info@muntersform.com, **USA** Phone +1 517 676 7070, aghort.info@munters.com, **Export & Other countries** Phone +39 0183 5211, info@munters.it

Your closest distributor