

Product sheet

Munters ML420

Desiccant dehumidifier
with AirC



Features

- Minimal energy consumption with modulating heating
- Multiple communication and external control options
- Multiple sensor support
- Maintenance schedules
- Alarm handling
- Dehumidifies efficiently down to -20°C
- Small footprint requires minimal floor area

Taking dehumidifiers into the future

For over half a century, Munters has been the leading pioneer within humidity control, and we're just getting started.

The ML420 desiccant dehumidifier with Munters AirC is designed to efficiently dehumidify in low moisture applications, and is equipped with a rotor casing in durable thermoset plastic which provides a precise balance for dehumidification and internal heat recovery in the airflows. Solid State heater control modulates the power for most energy efficient operation.

Munters AirC is a future-proof control system designed by Munters and provides flexibility and functionality like no other. It ensures your dehumidifier operates at its most energy efficient, and features advanced sensing, multiple communication support and alarm handling.

This technology represents 60 years of innovation and application knowledge for perfect control of the dehumidification process.



Munters ML420


Desiccant dehumidifier with AirC

Dimensions

A: Width	720 mm
B: Depth	600 mm
C: Height	1310 mm
D: Diameter	160 mm
E: Diameter	100 mm
Weight	141 kg

1. Process air in
2. Dry air out
3. Reactivation air
4. Wet air

Measurement diagram for reference only.




Technical specifications

Process air		
Rated airflow	(m ³ /h)	420
Available static pressure	(pa)	200
Reactivation air		
Rated airflow	(m ³ /h)	155
Available static pressure	(pa)	200
Miscellaneous data		
Operating temperature	(°C)	-20/+40
Sound power level to room Lw(A) dB, all inlets and outlets ducted	-	66
Air filter standard	-	G4
IEC protective class (unit)	-	IP33
IEC protective class (electrical)	-	IP54

Total power voltage & current (amps & phase)		
Total power, electrical	(kW)	4.57
200V 3-50Hz	(A)	14.9
200V 3-60Hz	(A)	14.9
220V 3-50Hz	(A)	12.6
220V 3-60Hz	(A)	12.6
230V 3-50Hz	(A)	12.1
230V 3-60Hz	(A)	12.1
380V 3-50Hz	(A)	7.3
380V 3-60Hz	(A)	7.3
400V 3-50Hz	(A)	7.0
415V 3-50Hz	(A)	6.7
440V 3-60Hz	(A)	6.4
460V 3-60Hz	(A)	6.1
480V 3-60Hz	(A)	5.9

Options

- Communication via Modbus
- Multiple sensors
- Blocked filter alarm
- External controls
- External filter box M5 or F7
- Insulated process air inlet
- Mirror handed
- Stainless steel casing



Find your nearest Munters office at www.munters.com

Munters reserves the right to make alterations to specifications, quantities, etc., for production or other reasons, subsequent to publication. © Munters AB, 2023